

D

C

B

A

4

3

2



1

4



3

2


1



PCB layout recommended :



3D view scale 1 : 1



TECHNICAL DATA

INSULATOR

Glass filled plastic UL94 V0



PLATING

Y = 1 Tin plated (thickness : Ni 2μ + Sn 5μ)

Y = 4 Gold plated (thickness : Ni 0.5μ mini. + Flash Au)

MECHANICAL SPECIFICATIONS

Mechanical endurance :

50 operations with tin plated

500 operations with gold plated

Insertion Force :

3 N max. with tin plated

1.5 N max. with gold plated

ELECTRICAL SPECIFICATIONS

Contact resistance : 20mΩ max.

AC current rating per contact 3A

Min. withstanding voltage 500V RMS

Min. insulator resistance 1000 MΩ

THERMAL SPECIFICATIONS

Connectors operating temperature : -40°C to +150°C


XX : Number of points : 02 to 25 points

 www.nicomatic.com Mail : nicomatic@nicomatic.fr Tel : +33 (0)4.50.36.13.85	e	06/10/2014	C.B.		V.G.
	Ind	Date	Drawn	Checked	Approved
Item : Walled header, right angle single row					
Folder : X:\Méthodes\Plans clients\Plans clients 2D\31 - Connecteurs et dérivés HE13-HE14\03-Connecteurs\1L-10-2Y1-XX-1.cl					

This document and drawings, sketches, and schematic drawings are the property of the NICOMATIC company. and no parts thereof may be reproduced and used without the written consent of the owner. Law dated 11.03.1902

Catalogue
Reference :

1L-10-2Y1-XX-1



General
tolerance

±0.1

Scale
3:1

Page
1/1

D

A4