





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECO-15-012503	02MAR2016	NK	JO



- 1

GOLD PLATING IS NOT REQUIRED IN THIS AREA.
- 2

CUT-OUTS ON THE BOX ARE AT MANUFACTURERS OPTION.
- 3

THIS TERMINAL IS REELED FOR THE STANDARD APPLICATOR.
- 4

THIS TERMINAL IS REELED FOR THE MINI APPLICATOR.
- 5

.000030 GOLD OVER .000050 NICKEL.
- 6

.000030 GOLD ON THE CONTACT AREA, GOLD FLASH ON THE REMAINDER ALL OVER .000050 NICKEL.
- 7

PREPLATED:(HALT).000078-.000158 BRIGHT TIN
- 8

POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS).
- 9

OBSOLETE PART NO.

87107-3	4	7	102348-3	87107-6
87107-8	4	6	102348-2	87107-5
87107-8	3	6	102348-2	_____
9 87107-7	4	5	102348-1	9 87107-2
9 87107-7	3	5	102348-1	_____
IN-PROCESS PART NUMBER	REMARKS	FINISH	LOOSE PIECE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L D RINGLY CHK J L GESFORD APVD J L GESFORD		12-10-85 12-16-85 12-16-85		 TE Connectivity							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		CONTACT, MOD IV, RECEPTACLE, CRIMP SNAP-IN							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-25,020 APPLICATION SPEC 114-25,003		SIZE A2		CAGE CODE 00779		DRAWING NO C=87107		RESTRICTED TO -	
		MATERIAL COPPER ALLOY, .008 THICK		FINISH SEE TABLE		WEIGHT -							
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV L					