


REVISIONS				DOC. NO. SPC-F004, Total Pages: 2 Effective: 7/15/97. DCP No: 229 Supersedes DCP No: 103				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
136	A	Released	J.W.M.	12/22/97	J.C.		B.B.	



NOTES:

Terminal:

1. Material: Copper
2. Finish: Electro-Tin Plate
3. Seamless

Tubing:

1. Multiple wall Polyolefin
2. Meltable, integral inner wall
3. 275°F [135°C] shrink temp.
4. -67°F [-55°C] to 230°F [110°C] continuous operating temp.
5. Tensile Strength: 2200 PSI
6. Ultimate Elongation: 500%
7. Secant Modulus, 2%: 27000 PSI
8. Specific Gravity: 1.00 Max.
9. Longitudinal Change: 5%
10. Dielectric strength: 1000V/Mil
11. Volume Resistivity: $10^{15} \Omega/\text{cm}$
12. Non-corrosive
13. Water Absorption: <0.1%
14. Tubing Color: Yellow

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

*Unless Otherwise Specified:
Dimensions are shown for
reference only!*

DRAWN BY:	DATE:
Jeff McVicker	12/22/97
CHECKED BY:	DATE:
JOHN COLE	1/12/97
APPROVED BY:	DATE:
BRETT BRAATZ	1/12/97

DRAWING TITLE:

Butt Connector

SIZE DWG. NO.

A

1682

ELECTRONIC FILE

92N3603.dwg

REV

A

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1