


Optical Level Switches

Dimensions



Operational principle

An optical level switch works by emitting a beam of infrared light within a prism and measuring the amount of light received. When the measured fluid reaches the sensor the amount of emitted light received drops thus triggering the contacts. As the sensor is detecting the state between material covering or not covering the prism it can be used to detect the presence or absence of fluid thus preventing damage to pumps.

The compact unit houses the infrared transmitter, the prism, the receiver and the electronics, there is also an external LED indicator to show the condition of the switch. The sensor requires a power supply of between 10-28 Volts Dc. The benefit of the modern optical sensor is that there are no moving parts that can retain material and get clogged up or damaged, simply fit and forget.

For ordering information please refer to the part number breakdown on the reverse of this brochure.

Applications


Liquid Level Control

In fig 4a two optical switches are installed individually in the upper and lower level of the tank.



When liquid rises to cover the upper optical switch it will trigger the solenoid valve to close. When the liquid level drops to the lower level the optical switch reopens the solenoid to refill the tank.

Motor protection

In Fig 4b an optical switch is installed in the lower level of the tank which will cut the power to the pump thus protecting it from damage.



Wiring

[illegible]



The Comus Group of companies

Order Information

Example: OPT-PC-AR-1 OPT- _ _ _ _ _

Housing Material

PC= Polycarbonate (Standard)

PS= Polysulfone

A2= 304 Grade Stainless Steel

A4= 316 Grade Stainless Steel

Connection Thread

AR= G 3/8" (BSP)

AU= 3/8 NPT (SS304 & SS316 only)

M2= M12 x 1.0 (Polycarbonate & Polysulfone only)

Output

1= PNP NC

2= PNP NO

3= NPN NC

4= NPN NO

*NO: Wet, In liquid NC: Dry, out of liquid

The full range of Comus products are available to view at any of the websites or contact your nearest distributor, a full list of our distributors can be found on the websites



The Comus International group of companies consists of:



Comus International
454 Allwood Road
Clifton
New Jersey 07012
U.S.A

Tel: (1)973 - 777 - 6900
Fax: (1)973 - 777 - 8405
email: info@comus-intl.com
Website: <http://www.comus-intl.com>
ISO 9001:2008
CERTIFICATE NO: 03-12314



Assemble Europe Limited
Unit 7, Rice Bridge Industrial Estate
Thorpe-le-Soken
Essex
England
CO16 0HL
Tel: +44 (0)1255 862236
Fax: +44 (0)1255 862014
email: sales@assemble.co.uk
Website: <http://www.assemble.co.uk>

ISO 9001:2008
CERTIFICATE NO: FM 21080



Comus Belgium BVBA
Overhaamlaan 40
B-3700 Tongeren
Belgium

Tel: +32 (0)12 390400
Fax: +32 (0)12 235754
email: info@comus.be
Website: <http://www.comus.be>



Comus International SARL
Immeuble 'Les Juiliottes'
31 Cours des Juiliottes
F-94700 Maisons-Alfort
France

Tel: +33 (0)1 43 968610
Fax: +33 (0)1 43 968611
email: info@comus.fr
Website: <http://www.comus.fr>



Switching Technologies Gunther
B-9-B-10, & C-1 Special Economic Zone (MEPZ)
Kadapperi
Tambaram
Chennai 600 045
India

Tel: +91 44 22628093
Fax: +91 44 22628271
email: stg@stg-india.com



Comus Electronics and Technologies
India Private Limited
No 3, Kamaraj Nagar 2nd Street
Tambaram Sanatorium
Chennai 600045
India
Tel: +91 44 43219090
Fax: +91 44 22628198
email: P.Ramesh@stg-india.com
chudan@comus-intl.com
Website: <http://www.comusindia.com>

We also have a large network of worldwide agents. These can be found on any of our websites, or on our company profile brochure



The Comus Group of companies

Optical Level Switches

