


AD2506 SERIES

External Dimensions



Specifications(Nominal)


*:Noise is measured at the distance of one (1)meter from the axis of intake.

Bearing type: ○=Ball ⚙=Sleeve ◯=1B1S ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	(CFM)	Maximum Pressure (InAq)	(mmAq)	*Noise Level (dB/A)	Weight (g)
25x25x06	AD0205DX-K50(X)	○●	5	0.051	0.255	7000	0.039	1.400	0.060	1.524	14.0	5.0
	AD0205LX-K50(X)	○●	5	0.086	0.430	9000	0.050	1.800	0.110	2.794	21.5	
	AD0205MX-K50(X)	○●	5	0.113	0.565	12000	0.067	2.400	0.185	4.699	29.0	
	AD0205HX-K50(X)	○●	5	0.148	0.740	14000	0.073	2.600	0.200	5.080	35.0	
	AD0212LX-K50(X)	○●	12	0.046	0.552	9000	0.050	1.800	0.110	2.794	21.5	
	AD0212MX-K50(X)	○●	12	0.060	0.720	12000	0.067	2.400	0.185	4.699	29.0	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以參考為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓	✓		✓							

*Safety approvals

✓	✓			✓