




10 Passende Gegenstecker siehe PN 829 868/966 194
MATING PARTS SEE PN 829 868/966 194

12 WITH STROKE LINE DRAWN VERSIONS NOT YET AVAILABLE

13 14 15 SIEHE BLATT 2 VON 2
SEE SHEET 2 OF 2

16 Außennuten eingeeignet,
Varianten siehe Blatt 2)
GROOVES ON OUTSIDE NARROWED, VERSIONS SEE SHEET 2

17 GLOW WIRE TEST 750°C ACC. DIN EN 60695-2-11
WITHOUT FLAME

18 OBSOLETE



19 PRELIMINARY PART, NOT FOR PRODUCTION

20 HOOK DIMENSION, NOT THE DIMENSION FOR MIDDLE WALL


21 PARTS WITH LOW INSERTION FORCE



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TWO ELECTRONICS CORPORATION IT IS OBSOLETE. IT SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN: 06JULY2019 CHG: 06JULY2019 BY: ATZMANN FOR: BORMUTH		 TE CONNECTIVITY	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±1°		NAME AMP DUOPLUG 2.5 SYSTEM PCB RAHMER AMP DUOPLUG 2.5 SYSTEM PCB FRAME (3-20 Posn)	
		APVD - PRODUCT SPEC - APPLICATION SPEC -		SIZE A I	
MATERIAL PA 6.6 25%GF UL94 V-0		FINISH - WEIGHT -		CAGE CODE -	
		CUSTOMER DRAWING		DRAWING NO C=964575	
				RESTRICTED TO -	
				SCALE 8:1 SHEET 1 of 2 REV D	



EXAMPLE:



KEYING BETWEEN CAVITY 10 AND 11

X-964 XXX-5
PART NO.

COLOR

- 16 COLOR: BLACK
- 14 COLOR: NATURAL (REDBROWN)
- 15 NATURAL (BEIGE)