

REV. Status

PRELIMINARY
02/16/00 MPHDSL transformer designed for use with Brooktree HDSL IC chip BT8970
at 2320Kbps rates


A. Electrical Specifications (@ 25°C)

1. Primary (Line side) Impedance; 135Ω
2. Secondary (IC side) Impedance; 32Ω
3. Longitudinal Balance; 50dBm MIN @ 80KHz TO 580KHz, 0dBm (Pin 9 grounded)
4. Frequency Response; ±0.25dB @ 80KHz to 580KHz, 0dBm
5. Insertion Loss; 0.5dB MAX @ 80KHz, 0dBm
6. Total Harmonic Distortion; -70dB MAX @ 80KHz, 1.85Vrms
7. Return Loss; 16.5dB MIN @ 80KHz to 580KHz, 0dBm
8. Primary Open Circuit Inductance; 1.0mH ±10% @ 10KHz, 0.1Vrms Measured (1-5) with 2 and 4 shorted
9. Leakage Inductance; 11μH MAX @ 100KHz, 0.1Vrms Measured (1-5) with 2 & 4, and 7 & 9 shorted
10. DC Current; 160mA
11. DC Resistance; (1-4)=0.95Ω ±10%
(2-5)=0.95Ω ±10%
(9-7)=0.85Ω ±10%
12. Turns Ratio; (1-4):(2-5)=1:1.00±2%
(7-9):(1-5)=1:2.00±2%
2 & 4 shorted
13. Dielectric Strength; 1875Vrms 1 second @ Pri to Sec



B. Marking; TTC-4018, TAMURA, date code and country of origin

C. Safety; Complies with UL1950 3rd Edition and IEC950

D. Schematic;



E. Mechanical Specifications;



MODEL NUMBER

TTC-4018

PREPARED BY:

D. Rund

ENGINEER:

M. Pitchai

QUALITY CONTROL:

D. Kelley

APPROVED:

J. Coleman

DWG CONTROL NO.

P-A1-12352

ACAD\TTC\A1123521.DWG

REV

PRE

HDSL

TRANSFORMER

TAMURA CORPORATION OF AMERICA

43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

TTC-4018

MODEL SPECIFICATION

DIM: mm(In) SCL: 2/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.