

1

2

3

4

5

6

D

X

X

S

3

3

E

6

X

X

0

9

L

F

SERIES

NO.OF CONTACTS

09,15,25,37

TYPE OF CONTACTS

S-SOCKET

TYPE OF TERMINATION

33-ANGLED SPILL

PITCH 2.84 USA

FOOT PRINT 8.08 USA

HEIGHT OF TERMINATION

E-2.00mm COMPATIBLE FOR 1.6mm PCB

RoHS INFORMATIONSDiv"\"This LF product meets European Union Directives and other country regulations as described in GS-22-008"\"The housing will withstand exposure to 260°C peak temperature for 30 seconds in a convection,infra-red or vapor reflow oven solder application.\"Packaging as per GS-14-920\"PRODUCT SPECIFICATION\"See :- GS-12-433\"PACKAGING SPECIFICATION\"See :- GS-14-1157\"SEE NOTE RoHS\"PACKAGING SPECIFICATION\"09- TRAY PACKAGING\"MOUNTING OPTIONS\"RV->LIF METAL PEG +F.SCREW LOCK UNC 4 40+METAL BRACKET\"RL->LIF METAL PEG+ INSERT M3+METAL BRACKET\"RX->LIF METAL PEG + INSERT UNC 4-40 +METAL BRACKET\"PLATING\"6->500 Mating/Un-mating performance\"4->200 Mating/Un-mating performance\"

FCI

FCIconnect.com

Copyright FCI

form: A3

1

2

3

4

5

6

1

2

3

4

5

6

1

2

3

4

5

6

1

2

3

4

5


6

mat'l. code				surface		tolerance		projection		product family							
SEE.TECH.SPEC				ISO 1302		ISO 406 ISO 1101				DELTA-D							
ltr	ecn no	dr	date	tolerances unless otherwise specified						title							
A	I07-0038	GVJ	07-03-16	angles	linear			MM		DELTA-D A/S FEMALE PIP CONNECTOR							
B	I08-0175	AS	09-01-14			.00±0.1				US VERSION							
C	I09-0162	AS	2009-08-13			.000±.00X		scale -									
				dr	ANISH.SALAM	2007-12-04				dwg no		sheet 1 of 2		size			
				engr	ANISH.SALAM	2009-08-13				C-DD-0099				A3			
				chr	ANISH.SALAM	2009-08-13											
				appd	ANISH.SALAM	2009-08-13				type		Product Customer		Drawing			
sheet index	revision sheet	C	C														
		1	2														


PDM: Rev:C

STATUS:Released

Printed: Jan 18, 2011






37	69.32	63.50	54.71	49.68
25	53.03	47.04	38.25	33.12
15	39.14	33.32	24.54	19.18
09	30.81	24.99	16.21	10.96
SHELL	A	B	D	E



PCB DRILLING & RECOMMENDED PAD DETAILS
(AFTER PLATING - THICKNESS 1.60MM)


SECTION A - A




TRUE POSITIONING : $\phi 0.36$

ACCESSORIES DETAILS

RV VERSION



RX/RL VERSION



mat'l. code SEE TECH. SPEC				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family DELTA-D			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title DELTA-D A/S FEMALE PIP CONNECTOR US VERSION			
A	I07-0167	AS	2007-12-04	angles	linear		dwg no C-DD-0099			
B	I08-0175	AS	2009-01-14	0° $\pm 1^\circ$		scale -	sheet 2 of 2			
C	I09-0162	AS	2009-08-13				size A3			
				dr	ANISH.SALAM	2007-12-04	type Product Customer Drawing			
				engr	ANISH.SALAM	2009-08-13				
				chr	ANISH.SALAM	2009-08-13				
				appd	ANISH.SALAM	2009-08-13				
sheet index	revision sheet	C	C							
		1	2							