



APPLICATION


LCR Polystyrene Capacitors are recommended for use in I.F transformers, tuned circuits, pulse networks, laboratory standards, timing circuits, analogue and digital computing circuits and many other applications where superior qualities are used to advantage.

LCR Polystyrene Film Capacitors offer:

- Low Temperature Coefficient
- Close capacitance tolerance
- Extreme capacitance stability
- Low power factor
- High Q
- High insulation resistance
- Small physical size

SPECIFICATION

Capacitance Range	10pF - 200,00pF
Capacitance Tolerance	$\pm 20\%$, $\pm 10\%$, $\pm 5\%$ $\pm 2.5\%$, or $\pm 1pF$
Voltage (DC working)	30, 63, 160, 400, 630V
Operating temperature range	-40°C to +85°C
Temperature Coefficient	N 150 \pm 50 ppm/°C
Power Factor	< 0.0005
Insulation Resistance (dry)	> 106 M Ω
Insulation Resistance (after humidity cycle)	>50,000 M Ω
Test Voltage	All caps tested at 2.5 times working voltage
Approvals	BS, EN, ISO 9001-2008



DESCRIPTION

Polystyrene is a superior dielectric material with exceptionally high insulation resistance and low loss.

Aluminium foil electrodes are used and terminal wires are welded to them to ensure satisfactory performance at low voltage and frequency.

Marking

Wherever possible capacitance, tolerance and working voltage are clearly indicated by black digital lettering, but on small components a letter code is used for tolerance and voltage (see overleaf)

CAPACITANCE TOLERANCE CODE

1pF	F
2.5%	H
5%	J
10%	K
20%	M

VOLTAGE LETTER CODE

30 V	Z
160 V	X
400 V	V
630V	U

CAPACITANCE STABILITY

Capacitor Length	Long Term Stability
10 mm and over	$\pm (0.2\% + 0.4pF)$
8 mm	$\pm (0.5\% + 0.4pF)$

TERMINATIONS: TINNED COPPER WIRE

Capacitor Length (mm)	Wire Diameter (mm)
8 mm	0.3
10 mm	0.4
over 10 mm	0.6

Twin twisted 0.6 mm wires are used on capacitors above 50,000 pF.