

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0858016027](#)
Status: **Obsolete**
Description: 2.00mm (.079") Pitch MFB™ (Futurebus+) Header, Vertical, Press-Fit Pin, 240 Circuits, 5 Rows

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Backplane Connectors
Series	85801
Application	Backplane
Comments	Backplane Header Module, Signal, Open
Component Type	PCB Header
Product Name	MFB™
Style	N/A

Physical

Circuits (Loaded)	240
Circuits (maximum)	240
Color - Resin	Natural
Durability (mating cycles max)	250
First Mate / Last Break	No
Keying to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Columns	N/A
Number of Pairs	Open Pin Field
Number of Rows	5
Orientation	Vertical
PC Tail Length	4.30mm (.169")
PCB Retention	None
PCB Thickness - Recommended	1.40mm (.055")
Packaging Type	Tube
Pitch - Mating Interface	2.00mm (.079")
Plating min - Mating	2.032µm (80µ")
Plating min - Termination	0.203µm (8µ")
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	1A
Data Rate	622.0 Mbps
Voltage - Maximum	1000V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-85801-010
---------------	--------------




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[85801Series](#)

Mates With
[54613](#) , [54526](#) , [54884](#) , [54867](#) , [54557](#) , [54883](#)

This document was generated on 05/18/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION