




N-Channel 60-V (D-S), 175°C MOSFET

PRODUCT SUMMARY

$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A)
60	0.018	60

175°C Rated
Maximum Junction Temperature
TrenchFET®
Power MOSFETs

TO-220AB




Top View

SUP60N06-18


DRAIN connected to TAB

TO-263



Top View

SUB60N06-18



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	60	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	I_D	60	A
	$T_C = 100^\circ\text{C}$		39	
Pulsed Drain Current		I_{DM}	120	
Avalanche Current		I_{AR}	60	
Repetitive Avalanche Energy ^a		E_{AR}	180	mJ
Power Dissipation	$T_C = 25^\circ\text{C}$ (TO-220AB and TO-263)	P_D	120 ^b	W
	$T_A = 25^\circ\text{C}$ (TO-263) ^c		3.7	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter		Symbol	Limit	Unit
Junction-to-Ambient	PCB Mount (TO-263) ^c	R_{thJA}	40	$^\circ\text{C/W}$
	Free Air (TO-220AB)		62.5	
Junction-to-Case		R_{thJC}	1.25	

Notes:

- a. Duty cycle $\leq 1\%$.
b. See SOA curve for voltage derating.
c. When mounted on 1" square PCB (FR-4 material).







For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>





SPECIFICATIONS (T _J = 25° C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA	60			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _{DS} = 1 mA	2.0		4.0	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 60 V, V _{GS} = 0 V			1	μA
		V _{DS} = 60 V, V _{GS} = 0 V, T _J = 125° C			50	
		V _{DS} = 60 V, V _{GS} = 0 V, T _J = 175° C			150	
On-State Drain Current ^a	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	60			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = 10 V, I _D = 30 A		0.014	0.018	Ω
		V _{GS} = 10 V, I _D = 30 A, T _J = 125° C		0.024	0.030	
		V _{GS} = 10 V, I _D = 30 A, T _J = 175° C		0.031	0.036	
Forward Transconductance ^a	g _{fs}	V _{DS} = 15 V, I _D = 30 A		49		S
Dynamic ^b						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 25 V, f = 1 MHz		2000		pF
Output Capacitance	C _{oss}			400		
Reverse Transfer Capacitance	C _{rss}			115		
Total Gate Charge ^c	Q _g	V _{DS} = 30 V, V _{GS} = 10 V, I _D = 60 A		39	60	nC
Gate-Source Charge ^c	Q _{gs}			12		
Gate-Drain Charge ^c	Q _{gd}			10		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = 30 V, R _L = 0.5 Ω I _D = 60 A, V _{GEN} = 10 V, R _G = 2.5 Ω		12	30	ns
Rise Time ^c	t _r			11	30	
Turn-Off Delay Time ^c	t _{d(off)}			25	50	
Fall Time ^c	t _f			15	30	
Source-Drain Diode Ratings and Characteristics (T _C = 25° C) ^b						
Continuous Current	I _S				60	A
Pulsed Current	I _{SM}				120	
Forward Voltage ^a	V _{SD}	I _F = 60 A, V _{GS} = 0 V			1.6	V
Reverse Recovery Time	t _{rr}	I _F = 60 A, di/dt = 100 A/μs		60		ns
Peak Reverse Recovery Current	I _{RM(REC)}			6.0		A
Reverse Recovery Charge	Q _{rr}			0.4		μC

Notes:




- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)****Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)



THERMAL RATINGS





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.