





LOC	DIST	REVISIONS					
BD	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-12-015665	26SEP12	KH	MZ



VIEW X-X
TYPICAL
SCALE 10:1




- | | |
|---|---|
| 1 | CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE. |
| 2 | 1.27um [.000050] MIN TIN OVER NICKEL FLASH. |
| 3 | 2.54um [.000100] MIN TIN-LEAD OVER 2.54um [.000100] MIN COPPER ON THIS END. |
| 4 | 2.54um [.000100] MIN TIN OVER 2.54um [.000100] MIN COPPER ON THIS END. |


4	213588-2
3	213588-1
POST FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C DORWART		2-23-90		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± ± —		PRODUCT SPEC — APPLICATION SPEC —		RECEPTACLE ASSEMBLY, 23-24, STANDARD SEX, POSTED CONTACTS, CPC	
MATERIAL		FINISH		WEIGHT —		SIZE A2 CAGE CODE 00779 DRAWING NO C-213588	
INSERT AND PIN: BRASS		—		—		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 2:1 SHEET 1 of 2 REV C	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
BD	0						
			-	SEE SHEET 1	-	-	-



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C DORWART 2-23-90		 TE Connectivity									
		CHK —											
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: —		APVD —		NAME							
	0 PLC ± —		PRODUCT SPEC		RECEPTACLE ASSEMBLY, 23-24, STANDARD SEX, POSTED CONTACTS, CPC								
	1 PLC ± —		—										
	2 PLC ± 0.13[.005]		—										
	3 PLC ± —		APPLICATION SPEC										
	4 PLC ± —		—										
ANGLES ± —		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL		FINISH		WEIGHT —		A2		00779		C=213588		—	
INSERT AND PIN: BRASS		—		CUSTOMER DRAWING		SCALE		2:1		SHEET		2 of 2	
										REV		C	