



1. MATERIAL:  
BODY - ALUMINUM, TIN PLATED  
SCREW - ALUMINUM, TIN PLATED
2. UL LISTED & CSA CERTIFIED FOR USE UP TO 600V & TEMPERATURE RATED 90°C (AL9CU)
3. DUAL RATED FOR USE WITH COPPER OR ALUMINUM STRANDED CODE CONDUCTOR
4. THESE PARTS ARE RoHS COMPLIANT
5. USE OF OXIDE INHIBITING JOINT COMPOUND LIKE PANDUIT CMP-100 RECOMMENDED FOR PAD TO PAD AND CONDUCTOR SURFACES
6. SEE PACKAGING LABEL FOR TIGHTENING TORQUE INFORMATION
7. PKG QTY:  
3 = 3



PART NUMBER	DIMENSIONS - IN [mm] +/- .02 [.5]										STUD SIZE	WIRE STRIP LENGTH	WIRE RANGE	HEX KEY*	
	A	B	D	G	T	H	W	C MAX.	J	K					
LAM2SA300-56-3	3.00 [76.2]	1.00 [25.4]	1.00 [25.4]	.47 [11.9]	.50 [12.7]	2.00 [50.8]	1.00 [25.4]	.53 [13.5]	1.38 [35.1]	.56 [14.2]	1.25 [31.8]	5/16	1.02 [25.9]	300kcmil-6 AWG	5/16

\* HEX SIZE MAY DIFFER FROM CHART. DIFFERENCE IN SIZE WILL NOT AFFECT FIT, FORM, OR FUNCTION OF PART

												PANDUIT CORP. TINLEY PARK, ILLINOIS			
												LAM2SA SERIES ALUMINUM MECHANICAL LUGS CUSTOMER DRAWING			
												UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) $\pm$ (.XX) $\pm$ (.XX) $\pm$ ANGLES $\pm$			
02	6/11	JHNU	RGB	B. REVISED PART NUMBER: LAM2SA300-56-3 WAS LAM2SA300-56-3Y				N41360BB-C41360	RGB	RGB	DRAWN BY CJW MAT'L: DATE 12/02 CHK'D	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	SCALE NONE DRAWING NO / CAD FILE C41360_02	DWG B SIZE	
01	9/10	JHNU	JHNU	A. REVISED DIMENSIONS FOR LAM2SA300-56				N41360BB-C41360	FLD	FLD					
00	2/06	JHNU	LEM	DRAWING RELEASED											
REV	DATE	BY	CHK	DESCRIPTION				ECN	-R	SUP					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[LAM2SA300-56-3](#)