

Silicon Carbide Schottky Diode


- Worlds first 600V Schottky diode
- Revolutionary semiconductor material - Silicon Carbide
- Switching behavior benchmark
- No reverse recovery
- No temperature influence on the switching behavior
- Ideal diode for Power Factor Correction up to 800W¹⁾
- No forward recovery
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC⁰⁾ for target applications

thinQ!™ SiC Schottky Diode


Product Summary

V_{RRM}	600	V
Q_C	13	nC
I_F	4	A


PG-TO220-2-2.



P-TO252



P-TO220



Type	Package	Ordering Code	Marking	Pin 1	Pin 2	Pin 3
SDP04S60	P-TO220-3	Q67040-S4369	D04S60	n.c.	C	A
SDD04S60	P-TO252-3	Q67040-S4368	D04S60	n.c.	A	C
SDT04S60	PG-TO220-2-2.	Q67040-S4445	D04S60	C	A	

Maximum Ratings, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Value	Unit
Continuous forward current, $T_C=100^\circ\text{C}$	I_F	4	A
RMS forward current, $f=50\text{Hz}$	I_{FRMS}	5.6	
Surge non repetitive forward current, sine halfwave $T_C=25^\circ\text{C}$, $t_p=10\text{ms}$	I_{FSM}	12.5	
Repetitive peak forward current $T_j=150^\circ\text{C}$, $T_C=100^\circ\text{C}$, $D=0.1$	I_{FRM}	18	
Non repetitive peak forward current $t_p=10\mu\text{s}$, $T_C=25^\circ\text{C}$	I_{FMAX}	40	
i^2t value, $T_C=25^\circ\text{C}$, $t_p=10\text{ms}$	$\int i^2 dt$	0.78	A ² s
Repetitive peak reverse voltage	V_{RRM}	600	V
Surge peak reverse voltage	V_{RSM}	600	
Power dissipation, $T_C=25^\circ\text{C}$	P_{tot}	36.5	W
Operating and storage temperature	T_j, T_{stg}	-55... +175	$^\circ\text{C}$

Thermal Characteristics

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Characteristics					
Thermal resistance, junction - case	R_{thJC}	-	-	4.1	K/W
Thermal resistance, junction - ambient, leaded	R_{thJA}	-	-	62	
SMD version, device on PCB:	R_{thJA}				
PG-TO252-3-1: @ min. footprint		-	-	75	
PG-TO252-3-1: @ 6 cm ² cooling area ²⁾		-	-	50	

Electrical Characteristics, at $T_j = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Static Characteristics					
Diode forward voltage $I_F=4A, T_j=25^{\circ}C$ $I_F=4A, T_j=150^{\circ}C$	V_F	- -	1.7 2	1.9 2.4	V
Reverse current $V_R=600V, T_j=25^{\circ}C$ $V_R=600V, T_j=150^{\circ}C$	I_R	- -	15 40	200 1000	μA

⁰J-STD20 and JESD22


¹CCM, $V_{IN} = 85\text{VAC}$, $T_j = 150^\circ\text{C}$, $T_C = 100^\circ\text{C}$, $\eta = 93\%$, $\Delta I_{IN} = 30\%$
²Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical without blown air.

Electrical Characteristics, at $T_j = 25\text{ °C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
AC Characteristics					
Total capacitive charge $V_R=400V, I_F=4A, di_F/dt=200A/\mu s, T_J=150^{\circ}C$	Q_C	-	13	-	nC
Switching time $V_R=400V, I_F=4A, di_F/dt=200A/\mu s, T_J=150^{\circ}C$	t_{rr}	-	n.a.	-	ns
Total capacitance $V_R=0V, T_C=25^{\circ}C, f=1MHz$ $V_R=300V, T_C=25^{\circ}C, f=1MHz$ $V_R=600V, T_C=25^{\circ}C, f=1MHz$	C	- - -	150 10 7	- - -	pF

1 Power dissipation


$$P_{\text{tot}} = f(T_C)$$



2 Diode forward current

$$I_F = f(T_C)$$


parameter: $T_j \leq 175^\circ\text{C}$



3 Typ. forward characteristic


$$I_F = f(V_F)$$

parameter: T_j , $t_p = 350 \mu\text{s}$




4 Typ. forward power dissipation vs. average forward current

$$P_{F(AV)} = f(I_F) \quad T_C = 100^\circ\text{C}, d = t_p/T$$



5 Typ. reverse current vs. reverse voltage


$$I_R = f(V_R)$$



6 Transient thermal impedance

$$Z_{thJC} = f(t_p)$$


$$\text{parameter : } D = t_p/T$$



7 Typ. capacitance vs. reverse voltage


$$C = f(V_R)$$

parameter: $T_C = 25^\circ\text{C}$, $f = 1\text{ MHz}$



8 Typ. C stored energy


$$E_C = f(V_R)$$




9 Typ. capacitive charge vs. current slope

$$Q_C = f(dI_F/dt)$$


parameter: $T_j = 150\text{ °C}$




P-TO220-3-1, P-TO220-3-21




DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.57	0.169	0.180
A1	1.17	1.40	0.046	0.055
A2	2.15	2.72	0.085	0.107
b	0.65	0.86	0.026	0.034
b1	0.95	1.40	0.037	0.055
b2	0.95	1.15	0.037	0.045
b3	0.65	1.15	0.026	0.045
c	0.33	0.60	0.013	0.024
D	14.81	15.95	0.583	0.628
D1	8.51	9.45	0.335	0.372
D2	12.19	13.10	0.480	0.516
E	9.70	10.36	0.382	0.408
E1	6.50	8.60	0.256	0.339
e	2.54		0.100	
e1	5.08		0.200	
N	3		3	
H1	5.90	6.90	0.232	0.272
L	13.00	14.00	0.512	0.551
L1	-	4.80	-	0.189
øP	3.60	3.89	0.142	0.153
Q	2.60	3.00	0.102	0.118




P-TO252-3-1, P-TO252-3-11, P-TO252-3-21 (D-Pak)





DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.159	2.413	0.085	0.095
A1	0.000	0.150	0.000	0.006
b	0.635	0.889	0.025	0.035
b2	0.650	1.150	0.026	0.045
b3	5.004	5.500	0.197	0.217
c	0.457	0.580	0.018	0.023
c2	0.460	0.980	0.018	0.039
D	5.969	6.223	0.235	0.245
D1	5.020	5.842	0.198	0.230
E	6.400	6.731	0.252	0.265
E1	4.850	5.207	0.191	0.205
e	2.286		0.090	
e1	4.572		0.180	
N	3		3	
H	9.400	10.480	0.370	0.413
L3	0.900	1.143	0.035	0.045
L4	0.584	0.950	0.023	0.037
L6	0.510	0.686	0.020	0.027
F1	10.500	10.700	0.413	0.421
F2	6.300	6.500	0.248	0.256
F3	2.100	2.300	0.083	0.091
F4	5.700	5.900	0.224	0.232
F5	5.660	5.860	0.222	0.231
F6	1.100	1.300	0.043	0.051

REFERENCE JEDEC TO252
SCALE 0 2.0 4mm
EUROPEAN PROJECTION 
ISSUE DATE 21-09-2005
FILE TO252_1

PG-TO-220-2-2



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.191	4.699	0.165	0.185
A1	1.170	1.400	0.046	0.055
A2	2.215	2.718	0.087	0.107
b	0.635	0.889	0.025	0.035
b2	0.950	1.651	0.037	0.065
c	0.330	0.635	0.013	0.025
D	14.808	15.950	0.583	0.628
D1	8.509	9.450	0.335	0.372
D2	12.850	14.245	0.506	0.561
E	9.677	10.363	0.381	0.408
E1	6.500	8.788	0.256	0.346
e	2.540		0.100	
e1	5.080		0.200	
N	2		2	
H1	5.900	6.900	0.232	0.272
L	12.700	14.000	0.500	0.551
L1	3.048	4.800	0.120	0.189
øP	3.550	3.886	0.140	0.153
Q	2.540	3.048	0.100	0.120

DOCUMENT NO. Z8B00003320
SCALE 
EUROPEAN PROJECTION 
ISSUE DATE 28-02-2007
REVISION 02

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2008 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.