





- FINISH**
CONTACTS: EITHER GOLD PLATED $0.76\mu\text{m}$ [.000030] MIN ON MATING END OR GOLD FLASH OVER PALLADIUM NICKEL, $0.76\mu\text{m}$ [.000030] MIN TOTAL ON MATING END. TIN-LEAD PLATED $3.05\mu\text{m}$ [.000120] MIN ON SOLDER LEAD, ALL OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL UNDERPLATE.
BACKET: NICKEL PLATED.
- POSITION TOLERANCE APPLIES AT TIP ONLY.**
- MATERIAL**
CONTACTS: PHOSPHOR BRONZE.
HOUSING: UL V-O RATED POLYESTER LCP COLOR BLACK.
BRACKET: ZINC.
- ACTUAL HOLE SIZE USED WILL DEPEND ON TRACE ROUTING REQUIREMENTS BETWEEN HOLES AND CONNECTOR PLACEMENT TECHNIQUE.**

50 POSITION AS SHOWN

X	31.11 [1.225]	84.20 [3.315]	62.23 [2.450]	66.60 [2.622]	68.94 [2.714]	78.23 [3.080]	100	749085-9
Y	15.24 [.600]	52.45 [2.065]	30.48 [1.200]	34.85 [1.372]	37.19 [1.464]	46.48 [1.830]	50	749085-5
PWB BOARD	S	R	P	N	M	L	NO.OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JACK ROOT 5-2-89	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK M.VISELLI 5-2-89	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APD R.WHITEMAN 5-3-89	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		
1 PLC ± -		SIZE		
2 PLC ± 0.38 [.015]		CAGE CODE		
3 PLC ± -		DRAWING NO		
4 PLC ± -		RESTRICTED TO		
ANGLES ± -		A1 00779 C=749085		
FINISH		SCALE 4:1		
CUSTOMER DRAWING		SHEET 1 OF 1		
		REV J		