






LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
	M	REVISED PER ECR-17-015775			03NOV2017	BDA	KR	




1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29 [1.030 - .090].
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. DIMENSIONS INDICATED ARE REFERENCE. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
4. NOTE DELETED.
5. UL AND CSA LOGOS LOCATED APPROXIMATELY AS SHOWN

RECOMMENDED CUT OUT



SUPERSEDED BY 1586887-1	NATURAL	9-794714-0
	BLACK	1-794714-9
	GRAY	1-794714-8
	BLUE	1-794714-6
	GREEN	1-794714-5
SUPERSEDED BY 794714-3	YELLOW	1-794714-4
	ORANGE	1-794714-3
	RED	1-794714-2
	BROWN	1-794714-1
	RED	794714-3
	NATURAL	794714-1
	COLOR	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. WHITAKER 06-OCT-1999	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK M. TRULL 06-OCT-1999	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. TRULL 06-OCT-1999	CAP. 6 CIRCUIT, UNIVERSAL MATE-N-LOK(TM), SPECIAL	
0 PLC ±.015 1 PLC ±.015 2 PLC ±.015 3 PLC ±.015 4 PLC ±.015		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
ANGLES ±.015		APPLICATION SPEC	A1 00779 C=794714	
FINISH		WEIGHT	RESTRICTED TO	
MATERIAL NYLON UL 94V-2, NATURAL		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV M	