

A


B

C


D

E


F




FRONT VIEW



SIDE VIEW



RECOMMENDED P.C.B. LAYOUT
 (COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT

MATERIALS:

PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL94V-0.

CONTACTS: PHOSPHOR BRONZE
 PLATING: REFER PART NUMBER FOR GOLD
 THICKNESS ON MATING SURFACES.
 50 μ " [1.27 MICRONS]
 MIN. NICKEL UNDERPLATE.
 100 μ " [2.54 MICRONS]
 MIN. MATTE TIN ON CONTACT TAILS.

PART NUMBER: RJE05-188-0X10

GOLD PLATING
 1 = 6 μ INCH
 2 = 15 μ INCH
 3 = 30 μ INCH
 4 = 50 μ INCH

DRAWN Chigow	DATE 25/01/06	Amphenol Canada Corp.		
DESIGNED				
CHECKED LCHAN	25/01/06			
I. E. APPRD.				
Q. A. APPRD.				
DWG. APPRD.		TITLE RJE05 SERIES MODULAR JACK, 8 POSITION, 8 CONTACTS, UNSHELDED, ULTRA LOW PROFILE-RoHS COMPLIANT		
ENG. REL. NO.				
REF.				
DIMENSIONS ARE IN mm	CODE ID. NO. 03554	DWG	DRAWING NO. P-RJE05-188-0X10	REV. A
WT.	SCALE	SURF.	SHEET 1 OF 1	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
 MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
 PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

A

B

C

D

E

F