





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C2	REV PER ECR 11-017004	16AUG11	JR	JH



SUGGESTED MATING TAB



- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
 - 2 - NO BURRS PERMISSIBLE AT HOLE.
 - 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
 - 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 CONTINUOUS STRIP ON REELS.
- 2 REF CRIMP INFORMATION:
WIRE CRIMP: .110 F TYPE
INSULATION CRIMP .180, F TYPE
- 3 #18-#14 AWG, 2.29-3.94 [.090-.155] DIA
OR TWO #18'S WITH 1.90 [.075] MAX INSULATION
- 4 PRELIMINARY - NOT FOR PRODUCTION



SECTION C-C
SCALE 10:1

SILVER 0.00381 [.000150] MIN	4 1217094-3
TIN 0.002032 [.000080] MIN	1217094-2
-	1217094-1
FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 6/19/98	 TE Connectivity						
		CHK MS FEHER 6/19/98							
DIMENSIONS: MM [INCHES]		APVD J GILLISPIE 6/19/98	NAME RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES —						
		PRODUCT SPEC —							
		APPLICATION SPEC 114-2074	SIZE A2	CAGE CODE 00779	DRAWING NO C-1217094		RESTRICTED TO —		
MATERIAL H06 BRASS		FINISH SEE TABLE	WEIGHT —	SCALE 5:1				SHEET 1 OF 1	REV C2
		CUSTOMER DRAWING							