

Industrial Rotary Position
Sensor

Spectrol Model 971 Rotary Position Sensor is suitable for demanding environments where long life and consistent linearity performance are required. Typical applications include Electrical Industrial Vehicles, Medical appliances, Automotive Systems and Controls, and Industrial & Commercial position sensing applications.

Spectrol's proven high performance conductive plastic resistive tracks and contact design achieves high accuracy. The 971 can be supplied with options for electrical track length, resistance, flying leads, integral connector and actuator drive direction.

ELECTRICAL**Total Resistance :**

5KOhms @ $\pm 20^{\circ}\text{C}$

Optional: 1KOhms to 25 KOhms

Resistance Tolerance:

$\pm 20\%$

Linearity (Independent):

$\pm 2\%$

Electrical Travel:

106°

Optional to 130° maximum

Maximum Power Rating:

1 watt @ 40°C ,
derated to zero @ 135°C

Output Smoothness:

0.3% maximum

Insulation Resistance:

1000MOhms Min 500 VDC

Temperature Coefficient of Resistance:

600 PPM/ $^{\circ}\text{C}$

Index Point (e/E):

3% $\pm 2\%$ @ -Low end stop

Maximum Voltage:

13.5 V d.c.

MECHANICAL**Rotation:**

$130^{\circ} \pm 2^{\circ}$ ccw

Optional: ccw or cw up to 140°
max $\pm 2^{\circ}$

Stop Strenght:

680 mNm Min.

End Play:

0.25mm Max.

Fixing Torque:

2 Nm Max.

Spring Torque:

Min Return - Nmm

Max wind up - 120 Nmm

Wire Pull Strenght:

10 Kg max (3 wires)

Lead Wires:

Nominal diameter 1.8mm. Length
optional

MARKING**Unit Identification:**

Manufacturer's name and model number, resistance value and tolerance, linearity specification date code and terminal identification.

OPTIONS**Integral Connector:**

AMP style Junior Timer mates with:

Housing: 1-8275782-1 (Unsealed)

Terminals: 927845-2

Housing: 282191-1 (Sealed)

Terminals: 929939-3

Wire Seales: 828904-1

Leads:

Standard: PVC..... + 85°C

High Temperature PVC... + 130°C

ENVIRONMENTAL

Vibration: 15g, 50-1000Hz

Shock: 50g

Rotational Life: 5,000,000 full cycles

10,800,000 dither cycles (Second rotation)

Temperature Range: - 40°C to + 85°C Wire version

- 40°C to + 155°C Connector version


Sealing: IP 5X (dust)

Humidity: 40°C 96% RH 504 Hours

SPECIAL FEATURES

- * High Performance, Compact Potentiometric Sensor
- * Rugged construction suitable for closed loop feedback applications
- * Through-hole actuation capability
- * Integral connector or flying lead versions
- * Actuator and mounting configuration options

DIMENSIONS



ORDERING INFORMATION

971

0001

Model

Version

0001 Connector

0002 Flying leads

ISO9001/QS9000



FM 26189



Spectrol Electronics Ltd, Garrard Way, Swindon SN3 3HY, UK. Tel: +44 (0) 1793 521351 Fax: 44 (0) 1793 525163 E-mail: sales@spectrol.co.uk

Spectrol Electronics Corporation, 4051 Greystone Drive, Ontario, CA 9176, USA. Tel: +1 (909) 923 3313 Fax: +1 (909) 923 3503 E-mail: spectrol@spectrol.com

Spectrol Electronics GmbH, Bauschstrasse 16, D73079 Suessen, Germany. Tel: +49 (0) 7162 7001 Fax: +49 (0) 7162 33546 E-mail: spectrol.gmbh@okay.net

Web Site: www.spectrol.com