





SECTION Z-Z



SECTION Y-Y



ACTUATOR CLOSE

部品構成

- ハウジング・・・材質：耐熱性樹脂 黒色 UL94V-0
HOUSING MATERIAL :HEAT RESISTANT POLYMER BLACK UL94-V0
- 奇数ターミナル・・・材質：銅合金
ODD TERMINAL MATERIAL :COPPER ALLOY
処理：ニッケル下地部分金メッキ（接触部及びテール部）
FINISH :PARTLY GOLD(CONTACT, TAIL) OVER NICKEL PLATING
- 偶数ターミナル・・・材質：銅合金
EVEN TERMINAL MATERIAL: COPPER ALLOY
処理：ニッケル下地部分金メッキ（接触部及びテール部）
FINISH :PARTLY GOLD(CONTACT, TAIL) OVER NICKEL PLATING
- アクチュエータ・・・材質：耐熱性樹脂 灰色 UL94V-0
ACTUATOR MATERIAL :HEAT RESISTANT POLYMER GRAY UL94-V0
- ネイル・・・材質：銅合金
NAIL MATERIAL: COPPER ALLOY
処理：ニッケル下地すずめっき
FINISH :TIN OVER NICKEL PLATING


RELEASED
EC NO: J2007-0951
2007/05/22
DRW:KUSATO
2007/05/22
CHKD:HIRATA
2007/05/22
APPR:HIRATA

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	±0.2
10 ^{OVER} 30 UNDER	±0.25
30 ^{OVER}	±0.3
ANGULAR	±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
K. TAKAHASHI	2006/07/28
CHECKED BY	DATE
H. HIRATA	2006/07/28
APPROVED BY	DATE
M. SASAO	2006/07/28
MATERIAL NO.	
SEE CHART	
SIZE	
A3	

SCALE 15:1	DESIGN UNITS METRIC	MATERIAL NO. _____ THIRD ANGLE PROJECTION 	
TITLE			
0.3 FPC CONN. ZIF E/O HSG ASSY (H=1.1)			
MOLEX INCORPORATED			
DOCUMENT NO. SD-501616-005		SHEET NO. 1 OF 2	

9.0	9.2	7.8	8.4	10.6	501616-2940	29
8.4	8.6	7.2	7.8	10.0	501616-2740	27
7.8	8.0	6.6	7.2	9.4	501616-2540	25
6.0	6.2	4.8	5.4	7.6	501616-1940	19
E	D	(C)	(B)	A	MATERIAL NO.	CIRCUIT



10

9

8

7

6

5

4

3

2


1

NOTES

1. 製品 (501616-**40) の詳細寸法については、
図面 SD-501616-005 をご参照下さい。
IN THE PACKAGE, PART NO. 501616-**40 DETAILED DIMENSIONS.
REFER TO SALES DRAWING NO. SD-501616-005.

2. 梱包数量 : 3000個/リール
NUMBER OF CONNECTORS : 3000 PCS/REEL

3. リードテープ長さ
LEAD TAPE LENGTH



4. 材料


キャリアテープ : ポリスチレン (PS)
トップテープ : PET, PE, PEF
リール : ポリスチレン (PS) <リサイクル材を含む>

MATERIAL

CARRIER TAPE : POLYSTYRENE (PS)
TOP TAPE : PET, PE, PEF
REEL : POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>

5. ELV及びRoHS適合品

ELV AND RoHS COMPLIANT



エンボステープ内の製品の向き

DIRECTION OF CONNECTOR IN
EMBOSSED TAPE

8.8	10.8	501616-2975	29
8.2	10.2	501616-2775	27
7.6	9.6	501616-2575	25
5.8	7.8	501616-1975	19
B	A	EMBOSSED PACKAGE オーダー番号 ORDER No.	極数 CIRCUIT

REVISED	EC NO.: J2009-4784	2009/01/26	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
	DRWN:MKAWABATA	2009/01/26		10 UNDER	± ---	DRAWN BY K. TAKAHASHI	DATE 2006/7/28	TITLE 0.3 FPC CONN. B/F EMBSTP PKG H=1.1		
	CHK'D:HSHI MOYAMA	2009/01/26		10 OVER 30 UNDER	± ---	CHECKED BY H. HIRATA	DATE 2006/7/28			
	APPR:HSHI MOYAMA	2009/01/26		30 OVER	± ---	APPROVED BY M. SASAO	DATE 2006/7/28		MOLEX INCORPORATED	
	ANGULAR ± --- °			MATERIAL NO.		DOCUMENT NO.		SHEET NO. 1 OF 1		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-501616-006				
	A	REV		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					