

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOCAD

DIST39

REVISIONS					
REV	DATE	DESCRIPTION	BY	CHK	APP
U1	12SEP07	ECO-07-000917	MB		NE
U2	24AUG09	REVISED PER ECO-09-020774	KK		AEG

(SEE TABLE FOR LOCATIONS)

.100 TYP KEYWAY

.250 ±.010

A SPACES AT .100 = B

C REF

.031 ±.001 TYP

.085 MAX

.125 ±.010

.063 ±.002

.587 ±.010

.062

.125 ±.010

.250 ±.010

.035

.040 +.000 - .015 2 PLC

.016 (M) TYP AT POST TIPS

.010 (M) TYP AT POST TIPS

.125 MIN

.156 ±.003 TYP TOLERANCE NON-CUMULATIVE

.055 ±.003 DIA TYP

KEYWAY LOCATIONS (REF-SEE TABLE)

(MATING LENGTH OF POST ON NEAR SIDE)

SCALE: 2:1

1

2

3

4

5

6

THESE SURFACES WILL NOT BE PLATED

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING

.000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL.

.000100-.000200 BRIGHT TIN OVER .000030 NICKEL.

ROHS 2002/95/EC COMPLIANT

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5	4	A,C,E,H,K,M,Q,S,U,W,Y	11	3.855	3.744	24	25	7-87267-5	
5	4	A,C,E,G,J,L,N,Q,S,U,W,Y	12	3.699	3.588	23	24	7-87267-4	
5	4	A,D,G,K,N,R,U,X	8	3.543	3.432	22	23	7-87267-3	
5	4	A,C,E,G,J,L,N,Q,S,U,W	11	3.387	3.276	21	22	7-87267-2	
5	4	A,D,G,K,N,R,U	7	3.231	3.120	20	21	7-87267-1	
5	4	A,C,E,G,J,L,N,Q,S,U	10	3.075	2.964	19	20	7-87267-0	
5	4	B,D,F,J,L,N,Q,S	8	2.919	2.808	18	19	6-87262-9	
5	4	A,D,F,J,M,P,S	7	2.763	2.652	17	18	6-87262-8	
5	4	A,D,G,K,N,R	6	2.607	2.496	16	17	6-87262-7	
5	4	A,C,E,G,J,L,N,Q	8	2.451	2.340	15	16	6-87262-6	
5	4	A,D,G,K,N	5	2.295	2.184	14	15	6-87262-5	
5	4	A,C,E,G,J,L,N	7	2.139	2.028	13	14	6-87262-4	
5	4	A,D,J,M	4	1.983	1.872	12	13	6-87262-3	
5	4	A,C,E,G,J,L	6	1.827	1.716	11	12	6-87262-2	
5	4	A,D,G,K	4	1.671	1.560	10	11	6-87262-1	
5	4	A,C,E,G,J	5	1.515	1.404	9	10	6-87262-0	
5	4	A,D,G	3	1.359	1.248	8	9	5-87262-9	
5	4	A,C,E	3	.891	.780	5	6	5-87262-6	
5	4	A,D	2	.735	.624	4	5	5-87262-5	
5	4	A,C	2	.579	.468	3	4	5-87262-4	
5	4	A	1	.423	.312	2	3	5-87262-3	
5	4	A	1	.267	.156	1	2	5-87262-2	
5	4	-	-	.111	-	-	1	5-87262-1	
5	4	A,C,E,G	4	1.203	1.092	7	8	2-87262-6	
6	OBSOLETE	3	A,C,E,H,K,M,Q,S,U,W,Y	11	3.855	3.744	24	25	2-87262-5
6	OBSOLETE	3	A,C,E,G,J,L,N,Q,S,U,W,Y	12	3.699	3.588	23	24	2-87262-4
6	OBSOLETE	3	A,D,G,K,N,R,U,X	8	3.543	3.432	22	23	2-87262-3
6	OBSOLETE	3	A,C,E,G,J,L,N,Q,S,U,W	11	3.387	3.276	21	22	2-87262-2
6	OBSOLETE	3	A,D,G,K,N,R,U	7	3.231	3.120	20	21	2-87262-1
6	OBSOLETE	3	A,C,E,G,J,L,N,Q,S,U	10	3.075	2.964	19	20	2-87262-0
6	OBSOLETE	3	B,D,F,J,L,N,Q,S	8	2.919	2.808	18	19	1-87262-9
6	OBSOLETE	3	A,D,F,J,M,P,S	7	2.763	2.652	17	18	1-87262-8
6	OBSOLETE	3	A,D,G,K,N,R	6	2.607	2.496	16	17	1-87262-7
6	OBSOLETE	3	A,C,E,G,J,L,N,Q	8	2.451	2.340	15	16	1-87262-6
6	OBSOLETE	3	A,D,G,K,N	5	2.295	2.184	14	15	1-87262-5
6	OBSOLETE	3	A,C,E,G,J,L,N	7	2.139	2.028	13	14	1-87262-4
6	OBSOLETE	3	A,D,J,M	4	1.983	1.872	12	13	1-87262-3
6	OBSOLETE	3	A,C,E,G,J,L	6	1.827	1.716	11	12	1-87262-2
6	OBSOLETE	3	A,D,G,K	4	1.671	1.560	10	11	1-87262-1
6	OBSOLETE	3	A,C,E,G,J	5	1.515	1.404	9	10	1-87262-0
6	OBSOLETE	3	A,D,G	3	1.359	1.248	8	9	87262-9
6	OBSOLETE	4	A,C,E,G	4	1.203	1.092	7	8	87262-8
6	OBSOLETE	4	A,C,E	3	1.047	.936	6	7	87262-7
6	OBSOLETE	3	A,C,E	3	.891	.780	5	6	87262-6
6	OBSOLETE	3	A,D	2	.735	.624	4	5	87262-5
6	OBSOLETE	3	A,C	2	.579	.468	3	4	87262-4
6	OBSOLETE	3	A	1	.423	.312	2	3	87262-3
6	OBSOLETE	3	A	1	.267	.156	1	2	87262-2
6	OBSOLETE	3	-	-	.111	-	-	1	87262-1
FINISH	KEYWAY LOCATIONS	NO OF KEYWAY	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN L A MAYER 4-15-87

CHK P de Jong 5-19-87

APVD J SCHIEFFER 5-19-87

NAME

PRODUCT SPEC 108-25016

APPLICATION SPEC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

SCALE

4:1

SHEET

1

OF

1

REV

U2

TYCO ELECTRONICS

Tyco Electronics Corporation

Harrisburg, Pa

HEADER ASSEMBLY, MOD I,

VERTICAL, SINGLE ROW,

.156

00779

87262

CUSTOMER DRAWING

AMP 4805 REV 31MAR2000