


DC 12025-02



SIZE :

120x120x25mm (4.72"x4.72"x0.98")

CONSTRUCTION :

Glass fiber reinforced plastic:

Impeller and housing PBT are UL 94V-0 rating

OPERATING TEMPERATURE :

Ball bearing - 30°C to +75°C

Sleeve bearing - 10°C to +70°C

INSULATION RESISTANCE :

10meg Ohm min. at 500 VDC

(between frame and terminal)

DIELECTRIC STRENGTH :

5mA max. at 500 VAC 60Hz one minute

(between frame and terminal)

FUNCTION :

auto-restart option

frequency generator or rotation detection signal option

WEIGHT :


150 grams

Specifications are subject to change without notice


Specifications

MODEL NO.	BEARING	RATED VOLTAGE	OPERATING VOLTAGE RANGE	RATED CURRENT	RATED INPUT POWER	SPEED R.P.M.	MAX. AIR FLOW		MAX. AIR PRESSURE		NOISE dB-A
		VDC	V	A	W		m³/min	CFM	mmH₂O	IN H₂O	
BP1202512L-02	Ball	12	10.2-13.8	0.25	3.00	1800	1.9	67.2	2.9	0.1	33.5
SP1202512L-02	Sleeve										
BP1202512M-02	Ball	12	10.2-13.8	0.38	4.56	2100	2.28	80.7	3.9	0.15	39.2
SP1202512M-02	Sleeve										
BP1202512H-02	Ball	12	10.2-13.8	0.50	6.00	2400	2.6	92.6	5.2	0.2	42.6
SP1202512H-02	Sleeve										
BP1202512HL-02	Ball	12	10.2-13.8	0.53	6.36	2700	2.9	103.7	6.3	0.3	47.1
SP1202512HL-02	Sleeve										
BP1202512HH-02	Ball	12	10.2-13.8	0.60	7.20	3000	3.4	119.1	7.6	0.3	48.3
SP1202512HH-02	Sleeve										

Dimensions (mm)



Performance Curve





DC 12025-02



SIZE :

120x120x25mm (4.72"x4.72"x0.98")

CONSTRUCTION :

Glass fiber reinforced plastic:

Impeller and housing PBT are UL 94V-0 rating

OPERATING TEMPERATURE :

Ball bearing - 30°C to +75°C

Sleeve bearing - 10°C to +70°C

INSULATION RESISTANCE :

10meg Ohm min. at 500 VDC

(between frame and terminal)

DIELECTRIC STRENGTH :

5mA max. at 500 VAC 60Hz one minute

(between frame and terminal)

FUNCTION :

auto-restart option

frequency generator or rotation detection signal option


WEIGHT :

150 grams Specifications are subject to change without notice


Specifications

MODEL NO.	BEARING	RATED VOLTAGE	OPERATING VOLTAGE RANGE	RATED CURRENT	RATED INPUT POWER	SPEED R.P.M.	MAX. AIR FLOW		MAX. AIR PRESSURE		NOISE dB-A
		VDC	V	A	W		m³/min	CFM	mmH₂O	IN H₂O	
BP1202524L-02	Ball	24	20.4-27.6	0.17	4.08	1800	1.9	67.2	2.9	0.1	33.5
SP1202524L-02	Sleeve										
BP1202524M-02	Ball	24	20.4-27.6	0.23	5.52	2100	2.28	80.7	3.9	0.2	39.2
SP1202524M-02	Sleeve										
BP1202524H-02	Ball	24	20.4-27.6	0.27	6.48	2400	2.6	92.6	5.2	0.2	42.6
SP1202524H-02	Sleeve										
BP1202524HL-02	Ball	24	20.4-27.6	0.30	7.20	2700	2.9	103.7	6.3	0.3	47.1
SP1202524HL-02	Sleeve										
BP1202524HH-02	Ball	24	20.4-27.6	0.35	8.40	3000	3.4	119.1	7.6	0.3	48.3
SP1202524HH-02	Sleeve										
BP1202548L-02	Ball	48	40.8~55.2	0.15	7.20	1800	1.9	67.2	2.9	0.1	33.5
SP1202548L-02	Sleeve										
BP1202548M-02	Ball	48	40.8~55.2	0.17	8.16	2100	2.28	80.7	3.9	0.2	39.2
SP1202548M-02	Sleeve										
BP1202548H-02	Ball	48	40.8~55.2	0.20	9.60	2400	2.6	92.6	5.2	0.2	42.6
SP1202548H-02	Sleeve										
BP1202548HL-02	Ball	48	40.8~55.2	0.23	11.04	2700	2.9	103.7	6.3	0.3	47.1
SP1202548HL-02	Sleeve										
BP1202548HH-02	Ball	48	40.8~55.2	0.25	12.00	3000	3.4	119.1	7.6	0.3	48.3
SP1202548HH-02	Sleeve										

Dimensions (mm)



Performance Curve



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bi-Sonic:

[BP1202512H W-G](#) [BP1202512L W-G](#) [BP1202512M W-G](#) [BP1202524H W-G](#) [BP1202524M W-G](#) [SP1202512M](#)
[SP1202524M](#) [BP1202512L-02](#) [BP1202512M-02](#) [BP1202512H-02](#) [BP1202524M-02](#) [BP1202524HH-02](#)
[BP1202548M-02](#) [BP1202548L-02](#) [SP1202512H](#) [SP1202524H](#) [BP1202512HL-02](#) [BP1202512HH-02](#) [BP1202524L-02](#)
[SP1202512L](#) [SP1202524L](#) [BP1202524H-02](#) [BP1202524HL-02](#) [BP1202548H-02](#) [BP1202548HL-02](#) [BP1202548HH-](#)
[02](#)