




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			




P.C.B LAYOUT

N=Number of poles

Dim A=N/2×9.52

Dim B=(N/2-1)×9.52



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

Material

- Terminal body (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Contacts: Brass
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 30A
- Wire range: Solid wire(AWG): 10-30 Stranded wire(AWG): 10-30
- Torque(Lb-In): 5.2
- Screw: M3
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety approval: US

RoHS Compliant

PART NUMBER

OSTVVXX2150

No. of Poles

04 2×2 Poles

06 2×3 Poles

... ..

24 2×12 Poles

COLOR:

0: Black

5: Green (Standard)

6: Blue

8: Grey



ON-SHORE TECHNOLOGY, INC.

	TITLE		OSTVV- 9.52mm series							
S	PART NO.		OSTVVXX2150			DWG NO.	OSTVVXX2150.DWG			
	APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
N	Shi Jun 2006.10.20		Marvin 2006.10.20	Marvin 2006.10.20	Marvin 2006.10.20			UNIT: mm	X.	±0.50
								SCALE: NONE	X.X	±0.30
								REV: E	X.XX	±0.10
						SHEET: 01/01		X°	±1°	