




PRODUCT NUMBER	NUMBER OF POS.	DIM "C"	DIM "D"
71998-Y02(H)LF	2 x 02	2.54	5.00
71998-Y03(H)LF	2 x 03	5.08	7.54
71998-Y04(H)LF	2 x 04	7.62	10.08
71998-Y05(H)LF	2 x 05	10.16	12.62
71998-Y06(H)LF	2 x 06	12.70	15.16
71998-Y07(H)LF	2 x 07	15.24	17.70
71998-Y08(H)LF	2 x 08	17.78	20.24
71998-Y09(H)LF	2 x 09	20.32	22.78
71998-Y10(H)LF	2 x 10	22.86	25.32
71998-Y13(H)LF	2 x 13	30.48	32.94

ROHS COMPATIBLE, SEE NOTE 4

WHEN NEEDED, SUFFIX LETTER "H" INDICATES IT'S A HIGH TEMPERATURE PRODUCT SEE NOTE 2

NOTES:

- MATERIAL, HOUSING: THERMOPLASTIC POLYESTER 30% GLASS FILLED COLOUR BLUE. FLAME RETARDANT PER UL-94 CATEGORY V0
- MATERIAL, HOUSING: HIGH TEMPERATURE THERMOPLASTIC 30% GLASS FILLED, COLOUR GREY. FLAME RETARDANT PER UL-94 CATEGORY V0.
- MATERIAL, TERMINAL: PHOSPHOR BRONZE EXTRA HARD.
- ROHS COMPATIBLE PRODUCT SPECIFICATIONS
- PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2um MINIMUM MATTE TIN OVER 1.27um MINIMUM NICKEL UNDERPLATE.
- MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- LEGAL STATEMENT: SEE GS-47-0004
- END STAND-OFFS FOR 2x2 UP TO 2x5 POS
NO END STAND-OFFS FOR 2x6 UP TO 2x60 POS

mo'tl. code	surface	tolerance	projection	product family
SEE NOTES	ISO 5002	ISO 446, ISO 1101	Ø	DX VCC DR
lfr	ECN no	date	tolerance unless otherwise specified	title
J F11-0043J00	12.02.22	angles	±0.3	KINKED
K B-191231LMU	14.10.20	linear		LEGS
E F06-0133DLE	06.02.27	dr	scale 10:1	dwg no
F F06-0204DLE	06.06.20	eng		71998
G F07-0198DLE	07.05.31	chr		customer
H F07-0271LMU	07.12.06	pppl		revision
index	sheet			
6	4			7151
				86