


ZoneBarrier Data

Protects sensitive I/O ports
against induced surges and
transients

- For 24V, 4-20mA current loop applications
- Industrial Ethernet compatible versions, UL Certified Cat.5
- Three stage protection including Gas Discharge Tube and Silicon Avalanche Diode technology
- Tested to IEC 61000-4-5 and CCITT K17
- 10 year product warranty



The ZoneBarrier range is a uniquely modular data and signal line protection system for 24V, 4-20mA current loop and Industrial Ethernet applications. By providing an effective barrier between uncontrolled transient environments and your valuable electronic systems the ZoneBarrier range protects you from costly system down time and equipment failure.

The sophisticated hybrid circuitry employed by the ZoneBarrier range protects your equipment without impeding normal operation. ZoneBarrier protection components comprise a combination of high energy Gas Discharge Tubes with ultra fast diodes and Silicon Avalanche Diodes. This combination of high quality surge protection components gives the ZoneBarrier range its characteristic low let-through voltage and high, 10kA, surge current capacity which provides excellent protection. ZoneBarrier devices have RJ45, terminal strip or pluggable terminal strip connectors.

Designed for multi-loop or single control loop applications the ZoneBarrier range offers a flexible surge protection solution that is capable of growing with your requirements. A ZoneBarrier module can be used as a stand-alone device or as a building block in a surge protection solution as simple or as complex as your requirements, now and in the future.

One simple manual operation clamps modules securely onto DIN rail, an action that also automatically provides the essential high-integrity ground connection. Standard 'Top-hat' (T-section) DIN rail is generally suitable for mounting ZoneBarrier range modules. Where a number of ZoneBarrier range modules are mounted on one rail, any that are incorrectly mounted (and therefore not securely grounded) are very obvious and can easily be remounted correctly. The ZoneBarrier range also has two mounting feet at either end of the unit, enabling mounting to a flat surface such as a cabinet wall.

ZoneBarrier data and signal devices are tested to IEC 61000-4-5 and CCITT K17. Industrial Ethernet compatible versions are also UL Certified Cat.5 and UL 497B Listed. ZoneBarriers come complete with a full 10 year product warranty.

Additional protection should be provided for other systems which may be inter-connected e.g. power feeds, telephone wiring etc., other units are available for this purpose.

ZoneBarrier Data

September 2016

SPECIFICATION

Maximum load current

0.5 Amps

Maximum surge current

4-20mA versions 10kA

100Base-T versions 8kA (1kA per line)

Maximum leakage current

5µA at working voltage (4-20mA versions)

Maximum in line resistance

< 5 ohms

Bandwidth

4-20mA versions 0.5 MHz

100Base-T versions 155 MHz

Ambient temperature limits

-40°F to +185°F (working)

-40°C to +85°C (working)

Humidity

95% RH (non-condensing)

Casing

Molded plastic

Weight

2.8oz (0.08Kg)

Dimensions

See figure 1

EMC compliance

BS EN 60950: 1992

BS EN 61000-6-2: 1999

INSTALLATION

All ZoneBarrier modules are installed in-line and are identified with "Protected" and "Un-protected" for fail-safe installation.

DIN rail mounting (figure 2)

ZoneBarrier modules can be mounted on any standard T-section DIN rail or on the optional 19" DIN rail assembly. To attach the ZoneBarrier module to the DIN rail, simply locate the DIN rail foot of the module over on edge of the DIN rail and then securely push the ZoneBarrier onto the DIN rail. Note the DIN rail must be properly grounded.

Stand-alone installation (figure 3)

To install a ZoneBarrier module as a stand-alone protector, attach an ground lead to the supplied ring terminal and secure this with the self tapping screw provided to the base of the unit. Using screws (or bolts) mount the module on any flat surface.

TO ORDER SPECIFY -

Model number as per specification table above

DIN rail mounting options

DR21607 5" DIN rail
for up to 4 ZoneBarriers

DR21649 17.5" DIN rail
for up to 16 ZoneBarriers

DR24500 19" DIN rail (with mounting
brackets) for up to 32 ZoneBarriers

Model	Type	Lines	Working voltage (V)	Limiting voltage (V)	Maximum continuous operating voltage (V)	Connectors
ZB24536	4-20mA	4 plus shield	24	30†	30	Terminal strip
ZB24539	4-20mA	2 plus shield	24	30†	30	Pluggable terminal strip
ZB24542	4-20mA	6	24	30†	30	Pluggable terminal strip
ZB24547	4-20mA	4 plus 2 shields	24	30†	30	Pluggable terminal strip
ZB24540	100Base-T*	8	5	10	N/A	RJ45
ZB24550	100Base-T	2 x 4	5	10	N/A	2 x RJ45




Figure 1 Dimensions




Figure 2 DIN rail installation




Figure 3 Stand alone installation

APPROVALS

Country	Standard/Authority	Approved for	Product
United States & Canada	UL 497B Listed UL Certified TIA/EIA 568-A Cat.5	Networks	ZB24540