

Dual Zero-Drift Operational Amplifier

February 2000

FEATURES

- Maximum Offset Voltage of $3\mu\text{V}$
- Maximum Offset Voltage Drift of $30\text{nV}/^\circ\text{C}$
- Small Footprint, Low Profile MS8 Package
- Noise: $1.5\mu\text{V}_{\text{P-P}}$ (0.1Hz to 10Hz Typ)
- Voltage Gain: 140dB (Typ)
- PSRR: 130dB (Typ)
- CMRR: 130dB (Typ)
- Supply Current: 0.75mA (Typ) per Amplifier
- Single Supply Operation: 2.7V to 11V
- Extended Common Mode Input Range
- Output Swings Rail-to-Rail
- Overload Recovery Time: 2ms (Typ)
- Operating Temperature Range -40°C to 85°C

APPLICATIONS

- Thermocouple Amplifiers
- Electronic Scales
- Medical Instrumentation
- Strain Gauge Amplifiers
- High Resolution Data Acquisition
- DC Accurate RC Active Filters

DESCRIPTION

The LTC[®]2051 is a dual zero-drift operational amplifier available in the MS8 and SO-8 packages. It operates from a single 2.7V supply while still supporting $\pm 5\text{V}$ applications. The power consumption is $750\mu\text{A}$ per op amp.


The LTC2051, despite its miniature size, features uncompromising DC performance. The typical input offset voltage and offset drift are $0.5\mu\text{V}$ and $10\text{nV}/^\circ\text{C}$. The almost zero DC offset and drift are supported with a power supply rejection ratio (PSRR) and common mode rejection ratio (CMRR) of more than 130dB.

The input common mode voltage ranges from the negative supply up to 1V from the positive supply. The LTC2051 also has an enhanced output stage capable of driving loads as low as $1\text{k}\Omega$ to both supply rails. The open-loop gain, loaded with $1\text{k}\Omega$, is in excess of 140dB. The LTC2051 also features a $1.5\mu\text{V}_{\text{P-P}}$ DC to 10Hz noise and a 3MHz gain bandwidth product.

 LTC and LT are registered trademarks of Linear Technology Corporation.


TYPICAL APPLICATION

High Performance Low Cost Instrumentation Amplifier



2051 TA01

Input Referred Noise 0.1Hz to 10Hz





LT2051 TA02

ABSOLUTE MAXIMUM RATINGS (Note 1)

Total Supply Voltage (V ⁺ to V ⁻)		Operating Temperature Range	-40°C to 85°C
LTC2051	7V	Specified Temperature Range (Note 3) ..	-40°C to 85°C
LTC2051HV	12V	Storage Temperature Range	-65°C to 150°C
Input Voltage	(V ⁺ + 0.3V) to (V ⁻ - 0.3V)		Lead Temperature (Soldering, 10 sec).....
Output Short-Circuit Duration	Indefinite		300°C

PACKAGE/ORDER INFORMATION

	ORDER PART NUMBER		ORDER PART NUMBER
 MS8 PACKAGE 8-LEAD PLASTIC MSOP $T_{JMAX} = 125^{\circ}\text{C}$, $\theta_{JA} = 250^{\circ}\text{C/W}$	LTC2051CMS8	 S8 PACKAGE 8-LEAD PLASTIC SO $T_{JMAX} = 125^{\circ}\text{C}$, $\theta_{JA} = 190^{\circ}\text{C/W}$	LTC2051CS8
	LTC2051IMS8		LTC2051IS8
	LTC2051HVCMS8		LTC2051HVCS8
	LTC2051HVIMS8		LTC2051HVIS8
	MS8 PART MARKING		S8 PART MARKING
	LTMN		2051
	LTMP		2051I
	LTPJ		2051HV
	LTPK		051HVI

Consult factory for Military grade parts.

ELECTRICAL CHARACTERISTICS: (LTC2051, LTC2051HV) The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25^{\circ}\text{C}$. $V_S = 3\text{V}$, 5V unless otherwise noted. (Note 3)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
Input Offset Voltage	(Note 2)		± 0.5	± 3	μV
Average Input Offset Drift	(Note 2) ●			± 0.03	$\mu\text{V}/^{\circ}\text{C}$
Long-Term Offset Drift			50		$\text{nV}/\sqrt{\text{mo}}$
Input Bias Current	$V_S = 3\text{V}$		± 8	± 50	pA
	$V_S = 3\text{V}$ ●			± 100	pA
	$V_S = 5\text{V}$		± 25	± 75	pA
	$V_S = 5\text{V}$ ●			± 150	pA
Input Offset Current	$V_S = 3\text{V}$			± 100	pA
	$V_S = 3\text{V}$ ●			± 150	pA
	$V_S = 5\text{V}$			± 150	pA
	$V_S = 5\text{V}$ ●			± 200	pA
Input Noise Voltage	$R_S = 100\Omega$, DC to 10Hz		1.5		μV_{P-P}
Common Mode Rejection Ratio	$V_{CM} = V^-$ to $V^+ - 1.3$, $V_S = 3\text{V}$	115	130		dB
	●	110	130		dB
	$V_{CM} = V^-$ to $V^+ - 1.3$, $V_S = 5\text{V}$	120	130		dB
	●	115	130		dB
Power Supply Rejection Ratio		120	130		dB
	●	115	130		dB

ELECTRICAL CHARACTERISTICS

The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25^\circ\text{C}$. $V_S = 3\text{V}$, 5V unless otherwise noted. (Note 3)

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
Large-Signal Voltage Gain	$R_L = 10\text{k}$, $V_S = 3\text{V}$		120	140		dB
		●	115	140		dB
	$R_L = 10\text{k}$, $V_S = 5\text{V}$		125	140		dB
		●	120	140		dB
Maximum Output Voltage Swing	$R_L = 2\text{k}$	●	$V^+ - 0.15$	$V^+ - 0.06$		V
	$R_L = 10\text{k}$	●	$V^+ - 0.05$	$V^+ - 0.02$		V
Slew Rate				2		V/ μs
Gain Bandwidth Product				3		MHz
Supply Current (2 Amplifiers)	No Load, $V_S = 3\text{V}$	●		1.5	2.0	mA
	No Load, $V_S = 5\text{V}$	●		1.7	2.4	mA
Internal Sampling Frequency				7.5		kHz

The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at $T_A = 25^\circ\text{C}$. $V_S = \pm 5\text{V}$ unless otherwise noted. (Note 3) (LTC2051HV)

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
Input Offset Voltage	(Note 2)			± 1	± 3	μV
Average Input Offset Drift	(Note 2)	●			± 0.03	$\mu\text{V}/^\circ\text{C}$
Long-Term Offset Drift				50		$\text{nV}/\sqrt{\text{mo}}$
Input Bias Current				± 90	± 150	pA
		●			± 300	pA
Input Offset Current					± 300	pA
		●			± 500	pA
Input Noise Voltage	$R_S = 100\Omega$, DC to 10Hz			1.5		$\mu\text{V}_{\text{P-P}}$
Common Mode Rejection Ratio	$V_{\text{CM}} = V^-$ to $V^+ - 1.3$		125	130		dB
		●	120	130		dB
Power Supply Rejection Ratio			120	130		dB
		●	115	130		dB
Large-Signal Voltage Gain	$R_L = 10\text{k}$		125	140		dB
		●	120	140		dB
Maximum Output Voltage Swing	$R_L = 2\text{k}$	●	4.80	4.92		V
	$R_L = 10\text{k}$	●	4.95	4.98		V
Slew Rate				2		V/ μs
Gain Bandwidth Product				3		MHz
Supply Current (2 Amplifiers)	No Load	●		2	3	mA
Internal Sampling Frequency				7.5		kHz

Note 1: Absolute Maximum Ratings are those values beyond which the life of the device may be impaired.


Note 2: These parameters are guaranteed by design. Thermocouple effects preclude measurements of these voltage levels during automated testing.

Note 3: The LTC2051C, LTC2051HVC is guaranteed to meet specified performance from 0°C to 70°C and is designed, characterized and expected to meet these extended temperature limits, but is not tested at -40°C and 85°C . The LTC2051I, LTC2051HVI is guaranteed to meet the extended temperature limits.


PACKAGE DESCRIPTION

Dimensions in inches (millimeters) unless otherwise noted.

MS8 Package 8-Lead Plastic MSOP (LTC DWG # 05-08-1660)



S8 Package 8-Lead Plastic Small Outline (Narrow 0.150) (LTC DWG # 05-08-1610)



RELATED PARTS

PART NUMBER	DESCRIPTION	COMMENTS
LTC1051/LTC1053	Precision Zero-Drift Op Amp	Dual/Quad
LTC1151	$\pm 15V$ Zero-Drift Op Amp	Dual High Voltage Operation $\pm 18V$
LTC1152	Rail-to-Rail Input and Output Zero-Drift Op Amp	Single Zero-Drift Op Amp with Rail-to-Rail Input and Output and Shutdown
LTC2050	Zero-Drift Op Amp in SOT-23	Single Supply Operation 2.7V to 6V, Shutdown

This datasheet has been downloaded from:

www.DatasheetCatalog.com

Datasheets for electronic components.