



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
AI	—		K4	ECR-12-020451	11NOV2013	KKB	RRP



- 1

2–5µm Sn über Ni in der crimpzone.
- 2

0.8µM Gold über Nickel in der kontaktzone
3. Für isolations Ø3.3–5.1 mm geeignet
- 4

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

4	OBSOLETE	926902-7	926899-7	CuZn30 F53	1	2
		926902-6	926899-6	CuSn4 F56	1	2
		926902-5	926899-5	CuCrZr F50	vorverzinnt	
		926902-4	926899-4	CuCrZr F50	blank	
		926902-3	926899-3	CuSn4 F56	vorverzinnt	
		926902-1	926899-1	CuZn30 F53	vorverzinnt	
		LOOSE PIECE	Bestell-Nr	werkstoff	Oberfläche	
					Farbe	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	11.11.03	TE TE Connectivity			
		CHK	12.11.03				
DIMENSIONS: mm		APVD	13.11.03	NAME UNIVERSAL M–N–L STIFT DGB 1.5–2.5 mm2			
		PRODUCT SPEC	—				
		APPLICATION SPEC	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		FINISH	—	A2	00779	C=926899	—
MATERIAL —		WEIGHT	—	CUSTOMER DRAWING			
		SCALE	5:1				
		SHEET	1 of 1	REV K4			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[926902-1](#)