



REVISIONS

P	LTR	DESCRIPTION	DATE	DN	APV
C		REVISED PER ECO-14-005095	15APR2014	AP	RP

- ① REFERENCE APPLICATION SPEC I14-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- ② MATERIAL:  
SHIELD - PHOSPHOR BRONZE  
CONTACT - COPPER-NICKEL-SILICON  
HOUSING, CHICKLET AND CHICKLET COVER - GLASS FILLED POLYESTER, UL 94V-0 RATED.
- ③ FINISH: CONTACT AND SHIELD MATING AREA:  
MEETS THE PERFORMANCE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPECIFICATION, 108-2055-1; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.  
COMPLIANT PIN AREA:  
0.5µm MIN BRIGHT TIN/LEAD OVER BASE PLATING.
- ④ CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN.
- ⑤ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- ⑥ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.  
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE I, NOVEMBER 1995.
- ⑧ FINISH: CONTACT AND SHIELD MATING AREA:  
MEETS THE PERFORMANCE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPECIFICATION, 108-2055-1; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.  
COMPLIANT PIN AREA:  
0.5µm MIN MATTE TIN OVER BASE PLATING.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DN: J.K.SHOBER 10JAN2009	APV: N.SCHROLL 10JAN2009
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC ±.01		1 PLC ±.01	2 PLC ±.01
3 PLC ±.01		4 PLC ±.01	5 PLC ±.01
MATERIAL: 12		FINISH: SEE TABLE	
APPLICATION SPEC		NAME: ASSEMBLY, Z-Pack Hm-Zd Plus, RECEPTACLE, 4 PAIR	
WEIGHT: -		SIZE: CAGE CODE: DRAWING NO: A100779C=2065657	
CUSTOMER DRAWING		RESTRICTED TO: -	

TE Connectivity