

NBF150

EMI Filter



How to Order:


NBF 150 - A - D

Series
Total Output Power

Options:
A- pins out side of unit
B- pins out bottom of unit
C- pins out top of unit
D- through hole inserts
(STD threaded)
I - M2.5 inserts


EMI COMPARISON GRAPHS

28V_{in} - 150 watts
MIL-STD-461D, CE101-4



28V_{in} - 150 watts
MIL-STD-461D, CE102

■ With NBF50
■ Without NBF50




FEATURES

- MIL-STD-461D Compliance CE101 and CE102
- Does Not Require External Components
- Meets Environmental Requirements of MIL-STD-810E and MIL-S-901
- For Use With NB80, NB100, NB150 Series DC/DC Converters

SPECIFICATIONS

Input Voltage (maximum)	50	Vdc
Rated Output Current	15	A
Isolation (Input/Output to Case)	500	Vdc
Operating Temperature	-55 to +100	°C
Storage Temperature	-55 to +125	°C
Insulation Resistance (measured at 50Vdc)	50	M Ohm
Weight	4.2	oz.
	120	grams
Size	3.0 x 2.0 x 0.38	inch
	76.2 x 50.8 x 9.7	mm
Volume	2.28	inch ³
	37.5	cm ³
Material	Pin	Brass (Solder Plating)
	Baseplate	Aluminum 5052-H32
	Case	28 Gauge Steel (cold rolled)
Finish		Nickel Plating
Mounting	Standard	4-40 inserts provided in baseplate
	I Option	M2.5 metric inserts (4 places)
	D Option	0.115 DIA thru holes (4 places)

CASE DRAWINGS



Tolerances:	inches	-	x.xx	= ±0.03
			x.xxx	= ±0.015
	mm	-	x.x	= ±0.8
			x.xx	= ±0.40