



Fastite® 2000™ 05LP




English	Français	Deutsch	Italiano	Español
Round large head Torx®	Tête ronde large Torx®	Rundkopf groß Torx®	Testa 1/2 Tonda con finta rondella Torx®	Cabeza alomada con ala Torx®
Steel case hardened* Hardness: Surface: > 450 HV0,3 Core: 290 to 370 HV10	Acier cémenté* Dureté: Superficielle: > 450 HV0,3 À coeur: 290 à 370 HV10	Stahl einsatzgehärtet* Härte: Oberfläche: > 450 HV0,3 Kern: 290 bis 370 HV10	Acciaio cementato* Durezza: Superficiale: > 450 HV0,3 A cuore: 290 a 370 HV10	Acero cementado* Dureza: Superficial: > 450 HV0,3 Núcleo: 290 a 370 HV10
Zinc alkaline clear ¹⁾ or Zinc -nickel alkaline clear ²⁾	Zinc alcalin claire ¹⁾ ou Zinc-nickel alcalin claire ²⁾	Zink alkalisch transparent ¹⁾ oder Zink-Nickel alkalisch transparent ²⁾	Zinco alcalino chiaro ¹⁾ o Zinco-Nichel alcalino chiaro ²⁾	Zincado y pasivado claro ¹⁾ o Niquelado ²⁾



¹⁾ 96 h / ²⁾ 720 h **

* : EN ISO 7085

** : to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo (ASTM B117)



Ø	Ø C	Ø D	Pitch / Pas/ Steigung/ Passo / Paso	Cp max.	Ø Dk	K	s ca.	Torx®	t	L	Part No/ref
MM3.0	2.93 - 3.02	2.88 - 2.97	2 x 0.5	1.70	6.00 - 6.60	2.40 - 2.77	0.8	T10	1.01 - 1.27	8 ±0.50	05LP3000801
										10 ±0.50	05LP3001001
										12 ±0.75	05LP3001201
										16 ±0.75	05LP3001601
										20 ±0.75	05LP3002001
										25 ±0.75	05LP3002501
MM4.0	3.92 - 4.02	3.85 - 3.95	2 x 0.7	2.20	9.00 - 9.50	3.20 - 3.60	1.0	T20	1.42 - 1.80	30 ±0.75	05LP3003001
										8 ±0.50	05LP4000801
										10 ±0.50	05LP4001001
										12 ±0.75	05LP4001201
										16 ±0.75	05LP4001601
										20 ±0.75	05LP4002001
MM5.0	4.91 - 5.02	4.83 - 4.94	2 x 0.8	2.90	10.50 - 11.00	3.65 - 4.08	1.2	T25	1.90 - 2.30	25 ±0.75	05LP4002501
										30 ±0.75	05LP4003001
										35 ±0.75	05LP4003501
										10 ±0.50	05LP5001001
										12 ±0.75	05LP5001201
										16 ±0.75	05LP5001601
MM5.0	4.91 - 5.02	4.83 - 4.94	2 x 0.8	2.90	10.50 - 11.00	3.65 - 4.08	1.2	T25	1.90 - 2.30	20 ±0.75	05LP5002001
										25 ±0.75	05LP5002501
										30 ±0.75	05LP5003001
										35 ±0.75	05LP5003501
										40 ±0.75	05LP5004001

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros



www.acument.com

© 2008 Acument Intellectual Properties, LLC

Torx® is a trademark of Acument Intellectual Properties, LLC. Fastite® 2000™ is Licensed by Research Engineering & Manufacturing, Inc. page 1/2
Data shown is subject to change without prior notice as a result of continuous product development and improvement policy.
Your local Acument Global Technologies representative is at your disposal should you need to confirm latest information.

Fastite® 2000™ 05LP

Ø	Ø C	Ø D	Pitch / Pas/ Steigung/ Passo / Paso	Cp max.	Ø Dk	K	s ca.	Torx®	t	L	Part No/ref
MM6.0	5.90 - 6.03	5.80 - 5.93	2 x 1.0	3.40	13.00 - 13.50	4.46 - 5.00	1.4	T30	2.28 - 2.67	12 ±0.75	05LP6001201
										16 ±0.75	05LP6001601
										20 ±0.75	05LP6002001
										25 ±0.75	05LP6002501
										30 ±0.75	05LP6003001
										35 ±0.75	05LP6003501
										40 ±0.75	05LP6004001
										45 ±0.75	05LP6004501
MM8.0	7.87 - 8.03	7.71 - 7.91	2 x 1.25	4.80	16.20 - 17.00	6.00 - 6.60	1.8	T40	2.79 - 3.18	16 ±0.75	05LP8001601
										20 ±0.75	05LP8002001
										25 ±0.75	05LP8002501
										30 ±0.75	05LP8003001
										35 ±0.75	05LP8003501
										40 ±0.75	05LP8004001
										45 ±0.75	05LP8004501
										50 ±0.75	05LP8005001

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Quality level / Niveau qualité / Qualitätsniveau / Livello qualità / Nivel de calidad: 150 ppm

Optional heat treatment : surface hardness 570 - 700 HV

Traitement thermique optionnel: dureté superficielle 570 - 700 HV


Optionale Wärmebehandlung: Oberflächenhärte 570 - 700 HV

Trattamento termico opzionale: durezza superficiale 570 - 700 HV

Tratamiento térmico opcional: Dureza superficial 570 - 700 HV

Highlighted part numbers are non standard, non in stock - Références surlignées non standard et non tenues en stock - Markierte Artikel-Nummern sind kein Standard, keine Lagerware - I codici evidenziati non sono standard, non sono a stock - Referencias no estándar, generalmente no en stock

Finishes / finition / Oberflächen / superficie / superficie

Type	Description / description / Beschreibung / descrizione / descripción			Code ⁴⁾
Standard	Zinc alkaline 8 µm mini clear, friction 0.12 - 0.18 / Zinc alcalin 8µm mini passivation claire, coefficient de frottement 0.12 - 0.18 / Zink alkalisch 8µm min. transparent, Reibkoeffizient 0.12 - 0.18 / Zinco alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.12 - 0.18 / Zincado y pasivado claro min. 8 µm coeficiente de fricción 0.12 - 0.18	✓	96 h	³⁾ AB
Optional	Zinc alkaline 8 µm mini clear, friction 0.12 - 0.18 / Zinc alcalin 8µm mini passivation claire, coefficient de frottement 0.12 - 0.18 / Zink alkalisch 8µm min. transparent, Reibkoeffizient 0.12 - 0.18 / Zinco alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.12 - 0.18 / Zincado y pasivado claro min. 8 µm coeficiente de fricción 0.12 - 0.18	✓	400 h	AC
Optional	Zinc-nickel alkaline clear, friction 0.12 - 0.18 / Zinc-nickel alcalin 8µm mini passivation claire, coefficient de frottement 0.12 - 0.18 / Zink-Nickel alkalisch transparent, Reibkoeffizient 0.12 - 0.18 / Zinco Nickel alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.12 - 0.18 / Niquelado claro min. 8 µm coeficiente de fricción 0.12 - 0.18	✓	720 h	BA
Optional	Zinc-nickel alkaline black, friction 0.12 - 0.18 / Zinc-nickel alcalin 8µm mini passivation noir, coefficient de frottement 0.12 - 0.18 / Zink-Nickel alkalisch schwarz, Reibkoeffizient 0.12 - 0.18 / Zinco Nickel alcalino 8µm min. passivazione nera, coefficiente d'attrito 0.12 - 0.18 / Niquelado negro min. 8 µm coeficiente de fricción 0.12 - 0.18	✓	720 h	BB

3) to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo

4) add code to the part number / ajoutez le code à la référence / fügen Sie den Code zur Artikel-Nummer hinzu / aggiungere il codice alla referenza / añadir numeración a la referencia



www.acument.com

© 2008 Acument Intellectual Properties, LLC

Torx® is a trademark of Acument Intellectual Properties, LLC. Fastite® 2000™ is Licensed by Research Engineering & Manufacturing, Inc. page 2/2

Data shown is subject to change without prior notice as a result of continuous product development and improvement policy. Your local Acument Global Technologies representative is at your disposal should you need to confirm latest information.

DS6012 - 01.2008