





MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
5	GP	00					0 RLSE NPR 5102, WAS 94-4163-024-10	07/11/94	-
							A REV PER EC 0020-1252-94	10/17/94	RF
							B REV PER EC 0020-1525-94	02/02/95	RF
							C REV PER EC 051A-0168-00	06/28/00	NF



- △ SHELL: CARBON STEEL; PIN CONTACT: PHOSPHOR BRONZE; HOUSING: POLYESTER, BLACK; PCB= FR-4 COPPERCLAD WITH SURFACE MOUNTED COMPONENTS ON TWO SIDES. JACKSCREW BODY: STAINLESS STEEL; JACKSCREW HEAD: PVC, BEIGE; COVER: ABS; SHIELD: COPPER.
- △ 5.08µm[0.000200] MIN TIN-NICKEL OVER 1.27µm[0.000500] MIN COPPER.
- △ 0.76µm[0.000030] MIN GOLD FOR A LENGTH OF 3.35[0.132] MIN FROM MATING END OVER 1.27µm[0.000500] MIN NICKEL.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.25 [0.010] 3 PLC DEC ± ANGLES ± -				DR 07/11/94 W.G.LENKER		AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL				CHK 10/19/94 R.STONE		NAME		
FINISH				APPD 10/19/94 R.FOWLER		PLUG ASSEMBLY, 68 POSITION, 27 LINE F.P.T., .050 SERIES AMPLIMITE™, TERMINATOR		
SHELL: △ CONTACTS: △				APPD 10/19/94 R.FOWLER		SIZE D		
APPLICATION SPEC				PRODUCT SPEC		CAGE CODE 00779		
WEIGHT				SCALE 4:1		DRAWING NO C-869867		
						SHEET 1 OF 1		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.