


PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)
OPERATING TEMPERATURE : -55°C TO 125°C
CONTACT RESISTANCE 20 mΩ MAX
INSERTION FORCE : 0.75N MAX/CONT
EXTRACTION FORCE : 0.15N MIN/CONT
INSULATION RESISTANCE : 10⁴ mΩ MIN

NOTES

1. " " LEAD FREE INDICATOR :LF=LEAD FREE
" " PERFORMANCE LEVEL INDICATOR (REF DWG NO.BSC .201844.003)
2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 00	KN	14-09-01
B	104-0109	ALEX E	27-11-04
C	DG05-0278	Kason	02-08-05
D	DG10-0110	NZ	2010.9.3
-	-	-	-
-	-	-	-

Material				Spec ref			
Mat code				✓			
Heat treat				1 DEC±0.2 1 DEC 2 DEC±0.1 2 DEC ANGLE±1° HOEKEN			
Plating/Finish				projection			
Dr	M.Fret	03-08-99		size A4			
Eng				Scale 2.000			
Chr				Model Name			
Appr				Model Revision			
				REL Level			
FCI				title MILLIPACS 2 / TYPE B / SHIELDED			
				dwg no BSC201907023			
				Rev. D			
Pro/E file				catalog no HM2S7IPE5101----			
				CUSTOMER DRAWING			
				sheet 1 of 1			