

132-00008

Button Head Tie w/ Retainers, Pilot Bushings , 130lb, 10.5", Max Bun Dia 2.87"

PA66HIRHS Black 50/pk

Article Number: 132-00008

Part Number: 132-00008

Type: BT130RDP

Material: PA66HIRHSUV




1. Base Data

Part No.	132-00008
Type	BT130RDP
Color	Black (BK)
Features	The button head tie is a two piece fixing tie providing for parallel entry and exit through the head. The strap contains serrations on both sides and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise

**Application**

Using a single hole these 'chassis ties' are widely used in the automotive, truck and heavy equipment markets.  
Ideal for applications which have access to both sides of the hole - example truck frame rails.

2. Product Dimensions



Min. Tensile Strength	130 lbs / 578 N
Length (L)	10.51 " / 267.0 mm
Width (W)	.30 " / 7.6 mm
Min. Ø Bundle	.06 " / 1.5 mm
Max. Ø Bundle	2.87 " / 73.0 mm

4. Material and Specifications

Material	Polyamide 6.6 high impact modified, heat-/UV-stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL94 HB

Material Head	PA66HS
---------------	--------

Operating Temperature -40 °F to +185 °F (-40 °C to +85 °C) continuous

Logistic and Packaging

Packaging Type	bag
----------------	-----

Pkg. Qty.	50
-----------	----

UPC 08930627176

## Cable Ties

### Button Head Ties

The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides and has two opposed pawls recessed within a domed head.

This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.



### New and Improved Features

The button head tie offers many new and improved features for added durability and installation ease.

**Standoff tabs** — prevent tie head from seating in button during strap insertion


**Pilot bushing** - protects the strap from abrasion on the mounting hole edge


**Ribs** - increased ribs added to the bottom of the button head for added durability

**Strap** - more radiused edges for added flexibility

**Serrations** - redesigned serrations and wedge design provide optimal strength when seated in the head


**Retainers** — lower retainers on BT130 help prevent the strap from backing out of the mounting hole and holds HellermannTyton's saddle mounts in place during assembly.



Button Head Ties *continued*

## Material Data

Cable Tie Material	<b>Polyamide 6.6 high impact modified, heat stabilized (PA66HIRHS)</b>
Button Head Material	<b>Polyamide 6.6 heat stabilized (PA66HS)</b>
Operating Temperature	<b>-40 °F to +221 °F (-40 °C to +105 °C) continuous</b>
Color	<b>Black</b>
Flammability	<b>UL94 HB</b>



Product Selection			Min. Tensile Strength		Length (L)		Max. Ø Bundle		Width (W)		Color	Pkg. Qty.
Article No.	Part No.	Type										
			lbs.	(N)	in.	(mm)	in.	(mm)	in.	(mm)		
BT105 Button Head Ties												
132-00010	132-00010	BT105R	105 lbs	(467)	9.63"	(244.4)	2.62"	(66.7)	.22"	(5.6)	Black	50
132-00011	132-00011	BT105L	105 lbs	(467)	15"	(381.5)	4.33"	(110)	.22"	(5.6)	Black	50
BT105 Button Head Ties with Pilot Bushings												
132-00006	132-00006	BT105RP	105 lbs	(467)	9.63"	(244.4)	2.62"	(66.7)	.22"	(5.6)	Black	50
132-00007	132-00007	BT105LP	105 lbs	(467)	15"	(381.5)	4.33"	(110)	.22"	(5.6)	Black	50
BT130 Button Head Ties with Retainers and Pilot Bushings												
132-00008	132-00008	BT130RDP	130 lbs	(578)	10.51"	(267.0)	2.87"	(73)	.30"	(7.6)	Black	50
132-00009	132-00009	BT130LDP	130 lbs	(578)	15"	(381.5)	4.33"	(110)	.30"	(7.6)	Black	50

Installation tools - MK9, MK9HT, MK9P. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.