

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 25-ft.

MODEL NUMBER: **P560-025**



Description

Tripp Lite's 25 foot DVI Dual Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Note: Review your monitor manufacturers specifications for a stated maximum DVI cable length. While many monitors only support a 5 meter (16ft) DVI cable, simply adding a Tripp Lite [B120-000](#) DVI Extender will guarantee full digital signal strength at any length up to 150ft. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual or Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI
- Dual Link digital signalling for transmission speeds to 9.9Gbps and 2560 x 1600 resolution
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors
- Check monitor manufacturers cable length specs - may need Tripp Lite [B120-000](#) DVI Extender

Specifications

General Info	
Product Group	DISPLAY & AUDIO CABLES
OVERVIEW	
Intended Application	Connecting Peripherals

Highlights

- For use with Dual or Single TMDS Link specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Check monitor manufacturers cable length specs - may need Tripp Lite [B120-000](#) DVI Extender

System Requirements

- Monitor with DVI, and CPU with Dual or Single Link DVI capabilities

Package Includes

- DVI Dual Link TMDS cable - DVI-D, M/M, 25'

Cable Type	DVI
Display Style	Direct Connect
Model Type	DVI
INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.62
UPC ASSIGNMENT	
Unit Carton UPC#	037332138804
PHYSICAL	
Color	Black
Style	DVI
CONNECTIONS	
Connector A	DVI-D DUAL LINK (MALE)
Connector B	DVI-D DUAL LINK (MALE)
Number of Connectors	2
CERTIFICATIONS	
Certifications	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.