


# ELFP SERIES PART NUMBERING SCHEME

| REV | ECN  | APPD         |
|-----|------|--------------|
| -   | 3600 | JEC 12/11/98 |
| A   | 3865 | JEC 11/9/99  |
| B   | 4686 | IQ 1/2/02    |
| C   | 4761 | IQ 2/20/02   |
| D   | 4821 | IQ 4/4/02    |
| E   | 5742 | 2W 12/28/05  |



COLOR/PLATING  
0=BLACK, TIN (STANDARD)  
1=BLACK, SELECTIVE GOLD  
G=GREEN, TIN  
1G=GREEN, SEL. GOLD

MOUNTING EARS  
0E=BLACK, TIN  
1E=BLACK, SEL. GOLD  
GE=GREEN, TIN  
EG=GREEN, SEL. GOLD

CONSULT PCD FOR PART NO. AND  
AVAILABILITY OF FOLLOWING OPTIONS:

- \* CUSTOM COLORS
- \* CUSTOM MARKING
- \* CUSTOM KEYING
- \* SELECTIVE CONTACT LOADING

**RATINGS**  
CURRENT - 15A  
VOLTAGE - 300V  
U.L. FILE NO. E83421

**RATINGS**  
CURRENT - 15A  
VOLTAGE - 300V  
CSA FILE NO. LR69703


DIN VDE 0627:1986  
DIN VDE 0110-1:1989  
EN 60947-1:1991  
EN 60947-7-1:1992

CURRENT - 15A  
VOLTAGE - 300 V  
TUV FILE NO. 20396

INSTALLATION  
RECOMMENDATIONS:  
WIRE RANGE: AWG #14-26, STRANDED  
OR SOLID; AWG #12 STRANDED  
WIRE STRIP LENGTH: .310"  
TIGHTENING TORQUE: 7 LB-IN.


MATERIALS:  
HOUSING: PPO, UL 94 V-0  
CONTACT: COPPER ALLOY, OPTIONAL FINISH  
SCREW: STEEL, NICKEL FINISH  
WIRE CLAMP: COPPER ALLOY, NICKEL FINISH  
OPERATING TEMPERATURE RANGE:  
-40°C-95°C

|                                           |                                                                                                                             |            |                                              |  |                                                                      |                      |  |             |              |
|-------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|------------|----------------------------------------------|--|----------------------------------------------------------------------|----------------------|--|-------------|--------------|
| DIMENSIONS                                | TOLERANCES                                                                                                                  | PROJECTION | <b>Amphenol Pcd</b><br>SPECIFICATION DRAWING |  | TITLE<br><br>ELFP SERIES<br>PLUGGABLE TERMINAL<br>BLOCK, RIGHT ANGLE |                      |  |             |              |
| ANSI Y14.5M<br>UNITS: INCHES<br>ACAD FILE | .XX ±.01<br>.XXX ±.005<br>ANGLES ±2°                                                                                        |            | ENGR<br>J. WILKINSON 11/8/98                 |  |                                                                      |                      |  |             |              |
| ORIGINAL<br>STAMPED<br>IN RED             | THIS DOCUMENT CONTAINS<br>PROPRIETARY INFORMATION WHICH<br>IS THE CONFIDENTIAL PROPERTY<br>OF AMPHENOL PCD INC. PEABODY, MA |            | CHKD<br>A. PATRIE 12/4/98                    |  | SIZE<br>A                                                            | DWG NO.<br>ELFP02110 |  | REV<br>E    |              |
|                                           |                                                                                                                             |            | APPD<br>J. CAHALY 12/11/98                   |  |                                                                      |                      |  |             |              |
|                                           |                                                                                                                             |            |                                              |  | CODE: 58982                                                          |                      |  | SCALE: NONE | SHEET 1 OF 2 |





# WITHOUT MOUNTING EARS

L=NUM OF POS X CL SPACING





2X .097 (.197 CL)  
.100 (.200 CL)



# WITH MOUNTING EARS

L=NUM OF POS X CL SPACING



| SIZE        | DWG NO.     | REV          |
|-------------|-------------|--------------|
| A           | ELFP02110   | E            |
| CODE: 58982 | SCALE: NONE | SHEET 2 OF 2 |