



REV	DOCUMENT	CHANGED BY	CHECK
2	202161	DLT 18JAN01	SAV
3	207439	TSM 13FEB03	SAV



NOTE

- 1 - PLUNGER MUST NOT PROTRUDE MORE THAN .002 ABOVE CASE WHEN AT FULL OVERTRAVEL
- 2 - RESTRICTED LISTING
- 3 - TERMINALS ARE SILVER PLATED

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:		DRAWN		DLT		18JAN01		Honeywell									
OPERATING FORCE----160 GRAMS MAX		CONTACT ARRANGEMENT S P D T		NO PLACE X ±.040 ±1		CHECK		SAV		18JAN01											
RELEASE FORCE-----20 GRAMS MIN		21A IHP 125, 250, 277 VAC 2HP 250, 277 VAC 		ONE PLACE .X ±.030 ±0,4		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.						TITLE SWITCH, BASIC									
DIFFERENTIAL TRAVEL-----.002-.010				TWO PLACE .XX ±.015 ±0,15																	
OVERTRAVEL-----0.037 MIN				THIRD ANGLE PROJECTION		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED						SIZE		DWG TYPE		DRAWING NAME				REV	
FREE POSITION -----.625 MAX												B		I		V7-1V10E9-000-2				3	
RELEASE TRAVEL-----.010 MIN						PTC 2D		ASME Y14.5M-1994		SCALE 2:1		WEIGHT		SHEET 1 OF 1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1V10E9-000-2](#)