







REV.	DATE	DESCRIPTION
NC	12/13/00	INITIAL RELEASE
A	05/06/07	REVISE BARREL/FERRULE DIMENSIONS/UPDATE DRAWING FORMAT
B	01/06/08	ADD CABLE CALL OUT IN DESCRIPTION. REMOVE NOTE 2



RECOMMENDED CABLE STRIPPING DIM'S



NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .128"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	G.R.S.						01/06/08	
7	HEAT SHRINK TUBE		BLACK	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED		PART DESCRIPTION						
6	HEX NUT	BRASS	NICKEL	1		ISSUED		MINI SMB BULKHEAD CRIMP JACK (FOR RG–179/U, 187/U CABLE)						
5	LOCK WASHER	BRASS	NICKEL	1		SHEET	1 OF 1							
4	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”			PART NO.						
3	CONTACT PIN	BRASS	GOLD	1				142179–75						
2	INSULATOR	TEFLON	NATURAL	1		CAD FILE	C:/142/142179–75.DWG						DWG. NO. 142179–75.DWG	
1	BODY	BRASS	NICKEL	1	DO NOT SCALE DRAWING									
	DESCRIPTION	MATERIAL	FINISH	QTY										