





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		R	EC 0G3C 0169 05	22APR05	BSV	JLG
			R1	REVISED PER ECO-09-020935	01SEP09	KK	AEG



RECOMMENDED HOLE LAYOUT



1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
2. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
3. PRELIMINARY PART – NOT RELEASED FOR PRODUCTION.
4. HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BALCK. POSTS: PHOSPHOR BRONZE.
5. .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
6. .000100-.000200 MATTE TIN OVER .000050 NICKEL.
7. HIGH TEMPERATURE CONFIGURATION.
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	OBSOLETE	7	6	NONE	2	.484	.400	4	9	10	5-146000-7
		7	6	NONE	13	1.284	1.200	12	25	26	5-146000-4
		7	6	NONE	5	.484	.400	4	9	10	5-146000-1
	3		5	NONE	3	.684	.600	6	13	14	1-146000-0
	3		5	1	NONE	.184	.100	1	3	4	146000-9
	3		5	NONE	6	1.184	1.100	11	23	24	146000-8
8	OBSOLETE		5	NONE	2	.484	.400	4	9	10	146000-7
	3		5	NONE	3	.284	.200	2	5	6	146000-6
	OBSOLETE		5	3	NONE	1.684	1.600	16	33	34	146000-5
8	OBSOLETE		5	NONE	13	1.284	1.200	12	25	26	146000-4
	OBSOLETE		5	NONE	10	.984	.900	9	19	20	146000-3
	OBSOLETE		5	NONE	6	.584	.500	5	11	12	146000-2
8	OBSOLETE		5	NONE	5	.484	.400	4	9	10	146000-1
		REMARKS	PLATING	ROW N	ROW M	C	B	A	NO OF ACTIVE POS	NO OF POS	ASSEMBLY PART NUMBER
				POST NUMBER OMITTED							