







- NOTES:
 1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. DIMS ARE SHOWN IN MM/INCH
 4.- XX REFERS TO THE NUMBER OF CIRCUITS
 5. ASSEMBLY IS ROHS COMPLIANT.



4	XX	SCREW #6-32X.250 BHD PHSLZN/STEEL	STEEL	ZN, CLEAR CHROMATE
3	2	PLATE MTG NI	BRASS	NICKEL PLATE
2	XX	TERM WW MED 6C SN/B	BRASS	TIN PLATE
1	1	BARRIER TERMINAL STRIP	PBT, UL 94V-0	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

INITIAL RELEASE	EC NO: ETC2008-0034	2007/08/22
DRWN: CLYORK	2007/09/12	
CHKD: JMACNEIL	2007/09/13	
APPR: JMACNEIL		
REV	DESCRIPTION	
A		

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.3	± ---
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	MM/IN
DRAWN BY	DATE
C. YORK	2007/08/16
CHECKED BY	DATE
J. MACNEIL	2007/08/16
APPROVED BY	DATE
J. MACNEIL	2007/08/16
MATERIAL NO.	
SEE CHART	
SIZE	B

SCALE	2:1
DESIGN UNITS	INCH
THIRD ANGLE PROJECTION	
TITLE	
9.53MM/.375 PCB BARRIER TERMINAL STRIP TERMINAL STYLE #3	
MOLEX INCORPORATED	
DOCUMENT NO.	SHEET NO.
SD-38729-048	1 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

NO. OF CIRCUITS	DIM. "A"		DIM. "B"		DIM. "C"		DIM. "D"		ASSEMBLY MATERIAL NO. (-75 OPT.)
	mm	in	mm	in	mm	in	mm	in	
02	40.1	1.58	9.53	.375	28.58	1.125	21.1	.83	387290459
03	49.7	1.96	19.05	.750	38.10	1.500	30.7	1.21	
04	59.2	2.33	28.58	1.125	47.63	1.875	40.2	1.58	387291019
05	68.7	2.71	38.10	1.500	57.15	2.250	49.7	1.96	387291468
06	78.2	3.08	47.63	1.875	66.68	2.625	59.2	2.33	387291639
07	87.8	3.46	57.15	2.250	76.20	3.000	68.8	2.71	387291018
08	97.3	3.83	66.68	2.625	85.73	3.375	78.3	3.08	387291469
09	106.8	4.21	76.20	3.000	95.25	3.750	87.8	3.46	
10	116.3	4.58	85.73	3.375	104.78	4.125	97.3	3.83	387291401
11	125.9	4.96	95.25	3.750	114.30	4.500	106.9	4.21	
12	135.4	5.33	104.78	4.125	123.83	4.875	116.4	4.58	387291581
13	144.9	5.71	114.30	4.500	133.35	5.250	125.9	4.96	387291643
14	154.4	6.08	123.83	4.875	142.88	5.625	135.4	5.33	
15	164.0	6.46	133.35	5.250	152.40	6.000	145.0	5.71	
16	173.5	6.83	142.88	5.625	161.93	6.375	154.5	6.08	
17	183.0	7.21	152.40	6.000	171.45	6.750	164.0	6.46	
18	192.5	7.58	161.93	6.375	180.98	7.125	173.5	6.83	
19	202.1	7.96	171.45	6.750	190.50	7.500	183.1	7.21	
20	211.6	8.33	180.98	7.125	200.03	7.875	192.6	7.58	
21	221.1	8.71	190.50	7.500	209.55	8.250	202.1	7.96	
22	230.6	9.08	200.03	7.875	219.08	8.625	211.6	8.33	
23	240.2	9.46	209.55	8.250	228.60	9.000	221.2	8.71	
24	249.7	9.83	219.08	8.625	238.13	9.375	230.7	9.08	
25	259.2	10.21	228.60	9.000	247.65	9.750	240.2	9.46	
26	268.7	10.58	238.13	9.375	257.18	10.125	249.7	9.83	

SEE SHEET #1 EC NO: ETC2008-0034 DRAWN: C. YORK 2007/08/12 CHKD: J. MACNEIL 2007/09/12 APPR: J. MACNEIL 2007/09/13	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE B	mm	INCH	TITLE 9.53MM/.375 PCB BARRIER TERMINAL STRIP TERMINAL STYLE #3			
				4 PLACES ± ---	± ---	DRAWN BY C. YORK	DATE 2007/08/16	MOLEX INCORPORATED	
				3 PLACES ± ---	± .005	CHECKED BY J. MACNEIL	DATE 2007/08/16		
A	REV	DESCRIPTION	MATERIAL NO.	APPROVED BY J. MACNEIL		DATE 2007/08/16	DOCUMENT NO. SD-38729-048		
				ANGULAR ± 2 °			SHEET NO. 2 OF 2		
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					