



A - _____ - B
B - _____ - A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

[illegible]

DIMENSIONS:		
meters		
		0 1 2 3 4

3 Restricted To:

QFN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK James Barry					
APVD James Barry					
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO C- 1906036		SHEET 1 of 4	REV A

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

8

7

6

5

4

3

2

1

Qty	U of M	Description	Item No.
2	piece	SC Simplex Housing, Beige	10
1	piece	LC Duplex clip, black	9
2	piece	SC Duplex Clip	8
AR	meter	2 fiber, 62.5/125, 2.0mm, Twinzip, Orange, OFNR (Riser)	7
2	piece	Trace Label	6
4	piece	LC, SC, FC Straight Boot, Beige	5
2	piece	2.5mm ferrule cover	4
4	piece	Eyelet/Shrink tube assembly - White	3
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	2
2	piece	CONN SUBASSY, MM, SC 1.6MM	1

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

5- Restricted To:

DWN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK James Barry		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD James Barry					
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO C- 1906036		SHEET 2 of 4	REV A

D

C

B

A

DING NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Rose		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1906036-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	-
4-1906036-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	-
4-1906036-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	-
4-1906036-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	-
4-1906036-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	-
4-1906036-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	-
4-1906036-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	-
5-1906036-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-
5-1906036-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	-
5-1906036-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	-
5-1906036-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	-
5-1906036-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	-
5-1906036-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	-
5-1906036-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	-
5-1906036-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	-
5-1906036-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	-
5-1906036-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	-
6-1906036-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	-
6-1906036-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	-
6-1906036-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	-
6-1906036-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	-
6-1906036-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	-
6-1906036-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	-
6-1906036-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	-
6-1906036-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	-
6-1906036-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	-
6-1906036-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	-
7-1906036-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	-
7-1906036-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	-
7-1906036-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	-
7-1906036-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	-
7-1906036-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	-
7-1906036-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	-
7-1906036-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	-
7-1906036-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	-
7-1906036-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	-
7-1906036-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	-
8-1906036-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	-

	A	Rev Per EC#	RELEASE	4/22/2009	-
P	LTR	REVISION RECORD		DATE	DIN

DIMENSIONS;
meters



TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Restricted To:

Cable Assy Configurator		MATERIAL		HEAT TREAT	
OK James Barry		-		-	
APVD James Barry		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex					
Secure to SC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO. C-1906036	SHEET 3 of 4	REV A	

D

C

3

A

TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES, AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES, AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

8

7

6

5

4

7

2

1

Label 1

Per specification 107-1645-1



-Trace # - Bar Code

[illegible]

-Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

-Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



—Trace # - Bar Code

[illegible]

—Trace # - Human Readable

Logo

Made in XXXX

X-XXXXXXXX-X

—Part Number

—Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	RELEASE	4/22/2009	-	JF			
P	LTR	REVISION RECORD			DATE	DIN	AP		

DIMENSIONS;
meters



TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Restricted To:

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT
CHK	James Barry	-	-
APVD	James Barry	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 1906036	4 of 4
			REV A