




- VDC: 5, 12, 24
- RPM: 2600~6200
- CFM: 2.27~5.64
- Impeller: 7 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 15g




DC FAN

40x40x11mm

Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
B4010B12L	●	12	0.06	4200	0.72	3.71	1.82	22.6	15
B4010S12L	○	12	0.06	4000	0.72	3.67	1.52	21.8	15
B4010B12M	●	12	0.07	5200	0.84	4.48	2.60	30.2	15
B4010B12H	●	12	0.07	6200	0.84	5.64	3.88	31.2	15
C4010B05L	●	5	0.08	4200	0.40	3.71	1.82	22.6	15
C4010S05L	○	5	0.08	4000	0.40	3.67	1.52	21.8	15
C4010B05M	●	5	0.15	5200	0.75	4.48	2.60	30.2	15
C4010B05H	●	5	0.16	6200	0.80	5.64	3.88	31.2	15
C4010B12L	●	12	0.06	4200	0.72	3.71	1.82	22.6	15
C4010S12L	○	12	0.06	4000	0.72	3.67	1.52	21.8	15
C4010B12M	●	12	0.07	5200	0.84	4.48	2.60	30.2	15
C4010B12H	●	12	0.10	6200	1.20	5.64	3.88	31.2	15
C4010B24L	●	24	0.06	4200	1.44	3.71	1.82	22.6	15
C4010S24L	○	24	0.06	4000	1.44	3.67	1.52	21.8	15
C4010B24M	●	24	0.07	5200	1.68	4.48	2.60	30.2	15
C4010B24H	●	24	0.08	6200	1.92	5.64	3.88	31.2	15
D4010B05L	●	5	0.11	4200	0.55	3.71	1.82	22.6	15
D4010S05L	○	5	0.11	4000	0.55	3.67	1.52	21.8	15
D4010B05M	●	5	0.13	5200	0.65	4.48	2.60	30.2	15
D4010B05H	●	5	0.15	6200	0.75	5.64	3.88	31.2	15
D4010B12L	●	12	0.06	4200	0.72	3.71	1.82	22.6	15
D4010S12L	○	12	0.06	4000	0.72	3.67	1.52	21.8	15
D4010B12M	●	12	0.07	5200	0.84	4.48	2.60	30.2	15
D4010B12H	●	12	0.10	6200	1.20	5.64	3.88	31.2	15
D4010B24L	●	24	0.06	4200	1.44	3.71	1.82	22.6	15
D4010S24L	○	24	0.06	4000	1.44	3.67	1.52	21.8	15
D4010B24M	●	24	0.07	5200	1.68	4.48	2.60	30.2	15
D4010B24H	●	24	0.08	6200	1.92	5.64	3.88	31.2	15
E4010B12H	●	12	0.06~0.15	2600~5200	0.72~1.80	2.27~4.48	0.84~2.60	22.9~30.2	15
F4010B12L	●	12	0.06	4200	0.72	3.71	1.82	22.6	15
F4010S12L	○	12	0.06	4000	0.72	3.67	1.52	21.8	15
F4010B12M	●	12	0.07	5200	0.84	4.48	2.60	30.2	15
F4010B12H	●	12	0.10	6200	1.20	5.64	3.88	31.2	15



Design specifics subject to change without notice.

STATIC PRESSURE

