



NORTON

NorZon Quick Cut



**Quick cutting and grinding without
contamination**

NORZON QUICK CUT

NorZon Quick Cut

Norton has a global reputation for its high quality and job focussed abrasive products. The superior bond technology and aggressive zirconia grain of the Norzon Quick Cut wheels provide quick cutting, fast material removal and high wheel life, which will decrease your total labour and abrasive cost.

The NorZon Quick Cut range offers a full, dedicated line of grinding and cutting-off wheels for stainless steel, hardened steel and cast iron applications. The extremely low level of iron, sulphur and chlorine elements in the NorZon Quick Cut wheel will guarantee no contamination of your workpiece or surface.



Application pictograms



Safety pictograms



Straight cutting-off wheels for angle grinders

ORDERCODE	PRODUCT CODE	EAN-CODE	DIMENSIONS	SPECIFICATION	M/S	MACHINE	SHAPE	
66252951007	455920	3157624559203	100x1,6x16,0	INOX_BNA 912	80	Angle Grinder	41	25
66252829663	376764	3157623767647	115x1,0x22,23	INOX_BNA 910	80	Angle Grinder	41	25
66252829496	643457	3157626434577	115x1,6x22,23	INOX_BNA 912	80	Angle Grinder	41	25
66252831458	643434	3157626434348	115x2,0x22,23	INOX_BNA 922	80	Angle Grinder	41	25
66252832682	376769	3157623767692	125x1,0x22,23	INOX_BNA 910	80	Angle Grinder	41	25
66252829577	643443	3157626434430	125x1,6x22,23	INOX_BNA 912	80	Angle Grinder	41	25
66252831463	643447	3157626434478	125x2,0x22,23	INOX_BNA 922	80	Angle Grinder	41	25
66252833117	643450	3157626434508	125x2,5x22,23	INOX_BNA 928	80	Angle Grinder	41	25
66252833118	643454	3157626434546	150x2,0x22,23	INOX_BNA 922	80	Angle Grinder	41	25
66252921570	643469	3157626434690	150x2,5x22,23	INOX_BNA 928	80	Angle Grinder	41	25
66252832870	376770	3157623767708	180x1,6x22,2	INOX_BNA 912	80	Angle Grinder	41	25
66252831469	643472	3157626434720	180x2,0x22,2	INOX_BNA 922	80	Angle Grinder	41	25
66252832734	643475	3157626434751	180x2,5x22,2	INOX_BNA 928	80	Angle Grinder	41	25
66252832683	376771	3157623767715	230x1,9x22,23	INOX_BNA 914	80	Angle Grinder	41	25
66252831478	643477	3157626434775	230x2,0x22,23	INOX_BNA 922	80	Angle Grinder	41	25
66252831474	643478	3157626434782	230x2,5x22,23	INOX_BNA 928	80	Angle Grinder	41	25



- Steel/inox
- Quick cutting time
- Long wheel life
- Iron, sulphur and chlorine free



BF42



- Steel/inox
- Quick cutting time
- Long wheel life
- Iron, sulphur and chlorine free



Depressed centre cutting-off wheels for angle grinders

ORDERCODE	PRODUCT CODE	EAN-CODE	DIMENSIONS	SPECIFICATION	M/S	MACHINE	SHAPE	
66252831502	642753	3157626427531	100x3,2x16,0	INOX_BDA 934	80	Angle Grinder	42	25
66252831506	642778	3157626427784	115x2,5x22,23	INOX_BDA 924	80	Angle Grinder	42	25
66252831510	642779	3157626427791	115x3,2x22,23	INOX_BDA 934	80	Angle Grinder	42	25
66252831516	642807	3157626428071	125x2,5x22,23	INOX_BDA 924	80	Angle Grinder	42	25
66252831519	643359	3157626433594	125x3,2x22,23	INOX_BDA 934	80	Angle Grinder	42	25
66252832730	643367	3157626433679	150x2,5x22,23	INOX_BDA 924	80	Angle Grinder	42	25
66252832731	643369	3157626433693	150x3,2x22,23	INOX_BDA 934	80	Angle Grinder	42	25
66252831524	643378	3157626433785	180x2,5x22,23	INOX_BDA 924	80	Angle Grinder	42	25
66252831527	643380	3157626433808	180x3,2x22,23	INOX_BDA 934	80	Angle Grinder	42	25
66252831529	643393	3157626433938	230x2,5x22,23	INOX_BDA 924	80	Angle Grinder	42	25
66252831532	643398	3157626433983	230x3,2x22,23	INOX_BDA 934	80	Angle Grinder	42	25

BF27



- Steel/inox
- Fast material removal
- Iron, sulphur and chlorine free
- Q-soft for fast material removal
- R-medium for universal applications
- S-hard for long wheel life



Depressed centre notching wheels for angle grinders

ORDERCODE	PRODUCT CODE	EAN-CODE	DIMENSIONS	SPECIFICATION	M/S	MACHINE	SHAPE	
66252950962	436962	3157624369628	125x4,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252832684	376773	3157623767739	125x4,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252950963	436965	3157624369659	180x4,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252832871	376774	3157623767746	180x4,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252950964	436966	3157624369666	230x4,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252832685	376777	3157623767777	230x4,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252833116	642761	3157626427616	100x4,6x16,0	INOX_R-Medium	80	Angle Grinder	27	25
66252832729	642780	3157626427807	115x4,6x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252829673	643362	3157626433624	125x4,6x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252832732	643371	3157626433716	150x4,6x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252831429	643382	3157626433822	180x4,6x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252831438	643399	3157626433990	230x4,6x22,23	INOX_R-Medium	80	Angle Grinder	27	25



BF27



- Steel/inox
- Fast material removal
- Iron, sulphur and chlorine free
- Q-soft for fast material removal
- R-medium for universal applications
- S-hard for long wheel life



Depressed centre grinding wheels for angle grinders

ORDERCODE	PRODUCT CODE	EAN-CODE	DIMENSIONS	SPECIFICATION	M/S	MACHINE	SHAPE	
66252832747	763932	3157627639322	125x7,0x22,23	INOX_Q-Soft	80	Angle Grinder	27	25
66252832745	731170	3157627311709	180x7,0x22,23	INOX_Q-Soft	80	Angle Grinder	27	25
66252832746	731171	3157627311716	230x7,0x22,23	INOX_Q-Soft	80	Angle Grinder	27	25
66252831403	642763	3157626427630	100x7,0x16,0	INOX_R-Medium	80	Angle Grinder	27	25
66252831412	642781	3157626427814	115x7,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252831421	643365	3157626433655	125x7,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252833119	643373	3157626433730	150x7,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252831433	643387	3157626433877	180x7,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252831446	643401	3157626434010	230x7,0x22,23	INOX_R-Medium	80	Angle Grinder	27	25
66252831404	642764	3157626427647	100x7,0x16,0	INOX_S-Hard	80	Angle Grinder	27	25
66252831413	642791	3157626427913	115x7,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252831422	643366	3157626433662	125x7,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252832733	643374	3157626433747	150x7,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252831434	643391	3157626433914	180x7,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25
66252831447	643402	3157626434027	230x7,0x22,23	INOX_S-Hard	80	Angle Grinder	27	25



Try them out!

To test the Norton Quick Cut range, just get in touch with your usual Norton contact.


SAINT-GOBAIN
ABRASIVES

Saint-Gobain Abrasives
European Headquarters
Rue de l'Ambassadeur – B.P. 8
78702 Conflans-Saint-Honorine
France

Tel : +33 (0)1 34 90 40 00
Fax : +33 (0)1 39 19 89 56

www.saint-gobain.com
www.nortonabrasives.com



www.fepa-abrasives.org



www.osa-abrasives.org



The personal safety of workers using abrasive cutting and grinding wheels is the primary concern of Norton and Saint-Gobain Abrasives. All Norton abrasive wheels are developed, manufactured and safety tested in accordance with the European standard Fepa "EN12413 - Safety requirements for bonded abrasive products". In addition, all Norton products meet the strict requirements of the international safety organisation oSa. Saint-Gobain Abrasives has an ISO 9001 certified quality management system.