







13	12	11	10	9	8	7	6	5	4	3	2	1
STRIP MATERIAL NUMBER	LOOSE PIECE MATERIAL NUMBER	AWG SIZE	FINISH			DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"			
194200001	194200009	16-14	PREPLATED TIN 75 μ MIN THICK OVER NICKEL FLASH			.235/5.97	.182/4.62	.141/3.58	.155/3.94	C		
194200002	194200010	22-18				.179/4.55	.143/3.63	.114/2.89	.106/2.70			
194200003	194200011	16-14	SELECT HARD GOLD 30 μ MIN. THICK WITH SELECT TIN 100 μ MIN. OVER NICKEL 50 μ MIN. OVERALL			.235/5.97	.182/4.62	.141/3.58	.155/3.94	C		
194200004	194200012	22-18				.179/4.55	.143/3.63	.114/2.89	.106/2.70			



SECTION A-A



GOLD PLATING AREA
INSIDE BOX



NOTES:

1. MATERIAL: COPPER ALLOY .0098/0.249 THK.
2. FINISH: SEE CHART.
3. TERMINALS FOR USE WITH 19418-**** RECEPTACLE HOUSING ASSEMBLY.
4. STRIP TERMINALS ARE REELED AS SHOWN ABOVE ON 24" REELS, 4000 PARTS PER REEL.
5. LOOSE TERMINALS ARE BULK PACKAGED IN QUANTITIES OF 400.
6. APPLICATION TOOLING AND CRIMP SPECIFICATIONS: 63865-6200 (14-16 AWG), 63865-6300 (14-16 AWG), 63811-4000 (HAND TOOL).

CORRECT DIM "C"
EC NO: WNA2012-0240
DRAWN/REV: 2011/11/03
CHKD: 2011/11/18
APPR:DTI/TUS

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .001
3 PLACES	± .010	± .002
2 PLACES	± .025	± .005
1 PLACE	± .050	± .010

ANGULAR ± 3 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY
JPAWLICK

DATE
05/05/03

CHECKED BY
JPAWLICK

DATE
05/05/03

APPROVED BY
RDEROSS

DATE
05/05/03

MATERIAL NO.
SEE CHART

SIZE
C

SCALE
4:1

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

TITLE
FEMALE RECEPTACLE
TERMINAL, 22-18 & 16-14
AWG, .059/1.50X.031/0.79

MOLEX INCORPORATED

DOCUMENT NO.
SD-19420-001

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION