

## Specification Status: Released

### Electrical Rating

**Voltage: 16V MAX**

**Current: 100A MAX**

### Insulating Material:

Cured, Flame Retardant Epoxy Polymer  
meets UL94 V-0 Requirements


### Lead Material:

20 AWG Tin Plated Copper  
(0.81mm [0.032] nom. diameter)

### Marking:

— Manufacturer's Mark  
X G7 and Part Identification

□ □ □ □ — Lot Identification



**TABLE I. DIMENSIONS:**

|      | A      |        | B      |        | C      |        | D      |     | E      |        | F      |
|------|--------|--------|--------|--------|--------|--------|--------|-----|--------|--------|--------|
|      | MIN    | MAX    | MIN    | MAX    | MIN    | MAX    | MIN    | MAX | MIN    | MAX    | TYP    |
| mm:  | 10.2   | 11.2   | 14.7   | 19.7   | 4.3    | 5.8    | 7.6    | -   | 2.0    | 3.0    | 1.2    |
| in*: | (0.40) | (0.44) | (0.58) | (0.78) | (0.17) | (0.23) | (0.30) | -   | (0.08) | (0.12) | (0.05) |

\*Rounded off approximation

**TABLE II. PERFORMANCE RATINGS:**

| I HOLD<br>RATED<br>CURRENT | CURRENT<br>RATINGS      |                         | INITIAL<br>RESISTANCE<br>VALUES |                        | TIME TO TRIP                   | R <sub>1</sub> MAX<br>1 HR. POST<br>TRIP<br>RESISTANCE<br>STANDARD<br>TRIP | TRIPPED-<br>STATE<br>POWER<br>DISSIPATION |
|----------------------------|-------------------------|-------------------------|---------------------------------|------------------------|--------------------------------|----------------------------------------------------------------------------|-------------------------------------------|
| AMPS<br>AT 25°C<br>HOLD    | AMPS<br>AT 25°C<br>HOLD | AMPS<br>AT 25°C<br>TRIP | OHMS<br>AT 25°C<br>MIN          | OHMS<br>AT 25°C<br>MAX | SECONDS AT<br>25°C, 35A<br>MAX | OHMS<br>AT 25°C<br>MAX                                                     | WATTS<br>AT 25°C<br>TYP                   |
| 7.0                        | 7.0                     | 11.9                    | 0.0077                          | 0.0131                 | 3.5                            | 0.0200                                                                     | 3.0                                       |

Agency Recognitions:  
Reference Documents:

UL, CSA, TUV.  
PS300

Precedence:

This specification takes precedence over documents referenced herein.

Effectivity:

Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

### Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Halogen Free\*

Directive 2002/95/EC  
Compliant

Directive 2000/53/EC  
Compliant



\* Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.