






	1	2	3	4	5	6	7	
A	     RECOMMENDED P.C.B LAYOUT (TOLERANCE:±0.05) NOTES: 1. MATERIAL: 1.1 HOUSING: PBT+30%G.F UL94V-0,BLUE COLOR. 1.2 4PIN CONTACT: PHOSPHOR BRONZE. 1.3 5PIN CONTACT: BRASS. 1.4 SHELL: BRASS 2.FINISH: 2.1 CONTACT: CONTACT AREA:15u"MIN Au PLATED SOLDER AREA: 100u"MIN TIN PLATED UNDER PLATE: 50u"MIN NI PLATED 2.2 SHELL: 80u"MIN NI PLATED 3. MECHANICAL: 3.1 MATING FORCE: 3.57kgf MAX. 3.2 UNMATING FORCE: 1.02kgf MIN 3.3 DURABILITY: 1500 CYCLES MIN 4. ELECTRICAL: 4.1 CURRENT RATING:1.0A. 4.2 DIELECTRIC STRENGTH: 500V AC FOR 1MINUTE. 4.3 CONTACT RESISTANCE: 30mΩ MAX. 4.4 INSULATION RESISTANCE: 100MΩ MIN 5. OPERATING TEMPERATURE: -55°C TO +85°C.							
B								
C								
D								
E								
F								
G	Scale Free TOLERANCE .X ±0.30 .XX ±0.20 .XXX ±0.10 DIM TOL X. ° ±5° Angle TOL UNIT mm Id. Modification Date 18.02.2014 Name Ray Date 18.02.2014 Name Ray Customer-No. ASSMANN WSW-No. Drawing-No. ASS 6300 CO Replace SHEET							
H								
	1	2	3	4	5	6	7	