



## Specification :

Current rating : 3 A, 250 V

## Surge Protection Data :

|                            |                  |
|----------------------------|------------------|
| Voltage                    | : 220 V to 240 V |
| Maximum operating voltage  | : 300 V ac (rms) |
| Mains three way protection | : LN LE NE       |
| Peak current               | : 4.5 kA         |
| Maximum energy             | : 3 × 125 J      |
| Maximum clamping voltage   | : 775 V          |
| Response time              | : <50 ns         |

## Standard :

BS 1363 / A; BS 5733 / A

## Conditions for Use :

An ambient temperature in the range -5°C to +40°C, the average value over 24 hours not exceeding 25°C

A situation not subject to exposure to direct radiation from the sun or other source of heat like to raise temperatures above the limits specified in a).

An altitude not exceeding 2,000 metres above sea level.

An atmosphere no subject to abnormal pollution by smoke, chemical fumes, rain, spray, prolonged periods of high humidity or other abnormal conditions.

## Safety Specifications

| Item                  | Conditions                      | Requirements                                                                                             |
|-----------------------|---------------------------------|----------------------------------------------------------------------------------------------------------|
| Appearance            | -                               | No defect such as cracks, deep scratches or blemishes                                                    |
| Marking               | -                               | Shall be legible and must be clear                                                                       |
| Insulation resistance | 500 + 250 V dc 1 minute         | Shall not be less than 5 MΩ                                                                              |
| Dielectric strength   | 2,000 ±60 V 1 minute            | No damage or breakdown                                                                                   |
| Resistance to aging   | 70° ±5° 168 hours               | No cracks or become sticky                                                                               |
| Construction          | 20° ±5°                         | Complied with figure 11, 12, 14, 16 gauge                                                                |
| Torque test           | Value of 0.6 Nm (6.1 kgf / cm)  | Terminal, cord grip and cover screws shall withstand the torque applied                                  |
| Glow wire test        | 650° / 750° electrically heated | Flame must extinguish within 30 seconds.                                                                 |
| Temperature rise      | 14 A, 250 V                     | Temperature rise must not exceed:<br>1. Terminals or terminations : 52 K<br>2. Accessible surface : 52 K |

## Safety Specifications

| Item                          | Conditions                                                                                              | Requirements                                                                              |
|-------------------------------|---------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| Make and break test of switch | 13 A, 250 V, 15,000 times                                                                               | Voltage drop across each switched pole shall not exceed 75 mV                             |
| Drop test                     | Fit with 3G 1.25 mm <sup>2</sup> cable, 2.25 m and drop at a height of 0.4 m above the floor            | No external damage which might affect safety and no components shall have become detached |
| Live parts accessibility      | Subjected to 1 mm test probe with applied force of 5 N when they are mounted and wired as in normal use | Live parts of socket shall not be accessible                                              |

## Construction

| Item | Description                    | Material                                                             |
|------|--------------------------------|----------------------------------------------------------------------|
| 1    | Socket base and cover          | FRPP                                                                 |
| 2    | Conductors (bus bar)           | Brass                                                                |
| 3    | Cover Screw                    | Mild steel nickel plated                                             |
| 4    | Switch                         | Nylon house with brass terminals                                     |
| 5    | Shutter                        | Nylon (PA)                                                           |
| 6    | Spring                         | Mild steel                                                           |
| 7    | Neon lamp with 220 KΩ resistor | Orange light                                                         |
| 8    | Neon lamp cover                | Polycarbonate (PC)                                                   |
| 9    | Switch Rocker                  | Polycarbonate (PC)                                                   |
| 10   | Surge component                | Metal oxide varistor + thermal fuse + neon indicator (if applicable) |
| 11   | Plug                           | 13 A BS 1363 plug                                                    |
| 12   | Cable                          | PVC, BS6500 3 × 1.25 mm <sup>2</sup>                                 |

## Part Number Table

| Description                          | Part Number |
|--------------------------------------|-------------|
| Extension Lead, 4 Gang, NDIV-SW, 2 M | 2814S       |
| Extension Lead, 6 Gang, NDIV-SW, 2 M | 2816SP      |
| Extension Lead, 8 Gang, NDIV-SW, 2 M | 2818SP      |

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro -ELEC is the registered trademark of the Group. © Premier Farnell plc 2012.