

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

04MAR2004

© COPYRIGHT 04MAR2004

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

J

-

0

RELEASED FJB0-0127-04



06APR2004

C.O

K.I




本図面に記載された内容はタイコ エレクトロニクス アンプ(株)の所有する情報を開示しております。
無断で複写・配布する事を禁じます。

特許出願中



参考パッド寸法
REFERENCE PCB PAD
(公差±0.05)

-1; 本図
-1; AS SHOWN



- △1 めっき仕様
全面Ni下地 : 0.8μm MIN
コンタクトポイント : Au 0.25~0.5μm
半田付けエリア : Au 0.05μm MIN
2. カットバリ : 0.05MAX
その他 全周バリ : 0.03MAX


△3 材料: 銅合金

- △1 PLATED
ALL OVER; Ni 0.8μm MIN
CONTACT POINT; Au 0.25~0.5μm
SOLDERING AREA; Au 0.05μm MIN
2. CUT BURR; 0.05 MAX.
OTHER BURR; 0.03 MAX.

△3 MATERIAL; COPPER ALLOY

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 概
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差 ±0.2
0-PLC ±
1-PLC ±0.5
2-PLC ±0.13
3-PLC ±0.013
4-PLC ±0.0001
ANGLES ±

MATERIAL

材料 SEE NOTE

FINISH

仕上 SEE NOTE

DWN 29JAN2004

C.OHASHI

CHK 06APR2004

T.KIMURA

APVD 06APR2004

K.IKEGAMI

PRODUCT SPEC

製品規格

108-5967

APPLICATION SPEC

取付適用規格

-

WEIGHT

計算値

0.01g

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME

名称

SHIELD FINGER 2411
ANTI OVER STRESS TYPE
EMBOSS PACKING

SIZE

CAGE CODE

DRAWING NO

番号

A3

00779

C=1746854

SCALE

尺度 15:1

SHEET

1

OF

2

REV

0

4

3

2

1



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

04MAR2004

© COPYRIGHT 04MAR2004 BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-	-	-	SEE SHEET 1	-	-





トレード部
160mmMIN
WITHOUT CHARGE

製品装填部
WITH PRODUCT CHARGE
5,000EA/REEL

300MIN
リーダー部 COVER TAPE
キャリアテープ空部 : 100mm MIN
WITHOUT CHARGE

剥離角度
PEELING ANGLE
165°~180°
剥離強度
PEELING FORCE
0.1N~1.0N

→ DIRECTION OF TOP OF REEL



- 1 ; AS SHOWN
- 1 ; 本 図

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN C. OHASHI 29 JAN 2004	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: mm		CHK T. KIMURA 06 APR 2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.2		APVD K. IKEGAMI 06 APR 2004	NAME SHIELD FINGER 2411 ANTI OVER STRESS TYPE EMBOSS PACKING	
0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ± FINISH		PRODUCT SPEC 108-5967 APPLICATION SPEC -		
MATERIAL SEE NOTE		WEIGHT 0.01g	SIZE A3	CAGE CODE 00779
FINISH SEE NOTE		CUSTOMER DRAWING	DRAWING NO C-1746854	RESTRICTED TO -
		SCALE 15:1	SHEET 2	OF 2
			REV 0	