


REV.	DATE	DESCRIPTION
A	01/28/03	REVISE BODY DIMENSIONS
B	04/29/04	REMOVE CENTER CONTACT PIN
C	12/30/04	MODIFY BARREL I.D. TO 1.7mm



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE	Amphenol Connex PART DESCRIPTION BNC R/A CRIMP PLUG - 75ohm (FOR RG-179 /U, 187A/U CABLE) PART NO. 112179 DWG. NO. 112179.DWG REV. C SIZE A SCALE NA			
7						DRAWN	G.R.S.	12/30/04				
6						CHECKED						
5	NUT	BRASS	NICKEL	1		ISSUED						
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1					
3	CONTACT PIN	BRASS	GOLD	1		CAD FILE		C:/112/112179.DWG				
2	INSULATOR	DELIN	NATURAL	1								
1	SHELL/BODY	BRASS	NICKEL	1								
	DESCRIPTION	MATERIAL	FINISH	QTY								