















- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR-BRONZE.
- 3 CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) –
0.00127 MIN. NICKEL
ON MATING SURFACES–
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT
ON LEADS–
0.00381 MIN. TIN-LEAD, OVER UNDERPLATE
LUBRICATION (ENTIRE CONTACT)
SURFACE CONDITIONER PER AMP SPEC. 112-1002 AFTER PLATING.
- 4 PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED
APPROXIMATELY AS SHOWN.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	NO	34	17	35.88		72	1-536507-1
OBSOLETE	NO	130	65	131.88		264	1-536507-0
 OBSOLETE	NO	106	53	107.88		216	536507-9
	NO	118	59	119.88		240	536507-8
	NO	70	35	71.88		144	536507-7
OBSOLETE	NO	58	29	59.88		120	536507-6
	NO	82	41	83.88		168	536507-5
	NO	94	47	95.88		192	536507-4
	NO	46	23	47.88		96	536507-3
	NO	22	11	23.88		48	536507-2
	YES	10	5	11.88		24	536507-1
POSITIONING PEGS		C	B	A	FINISH	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.R.BENDER / 08/06/92	 TE Connectivity					
DIMENSIONS: mm		CHK S.HEADER 01/26/93	NAME					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. PEOPLES 01/26/93	RECEPTACLE ASSEMBLY, SIGNAL MODULE, Z-PACK 2mm FB, 4 ROW, 2.73mm LEAD LENGTH					
0 PLC ± -		PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
1 PLC ± -		—						
2 PLC ± .13		APPLICATION SPEC						
3 PLC ± -		—						
4 PLC ± -		WEIGHT		A1 00779		C=536507	—	
ANGLES ± -								
FINISH								
MATERIAL								
				CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV AA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-536507-0](#)