BUF460AV

NPN TRANSISTOR POWER MODULE

- EASY TO DRIVE TECHNOLOGY (ETD)
- HIGH CURRENT POWER BIPOLAR MODULE
- VERY LOW R_{th} JUNCTION CASE
- SPECIFIED ACCIDENTAL OVERLOAD AREAS
- FULLY INSULATED PACKAGE (U.L. COMPLIANT) FOR EASY MOUNTING
- LOW INTERNAL PARASITIC INDUCTANCE

APPLICATIONS:
- MOTOR CONTROL
- SMPS & UPS
- WELDING EQUIPMENT



ISOTOP

INTERNAL SCHEMATIC DIAGRAM



ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
V_{CEV}	Collector-Emitter Voltage (V_{BE} = -5 V)	1000	V
$V_{CEO(sus)}$	Collector-Emitter Voltage (I_B = 0)	450	V
V_{EBO}	Emitter-Base Voltage (I_C = 0)	7	V
I_C	Collector Current	80	A
I_{CM}	Collector Peak Current (t_p = 10 ms)	160	A
I_B	Base Current	18	A
I_{BM}	Base Peak Current (t_p = 10 ms)	27	A
P_{tot}	Total Dissipation at T_c = 25 ^oC	270	W
V_{isol}	Insulation Withstand Voltage (RMS) from All Four Terminals to External Heatsink	2500	
T_{stg}	Storage Temperature	-65 to 150	^oC
T_j	Max Operation Junction Temperature	150	^oC

THERMAL DATA

$R_{thj-case}$	Thermal Resistance Junction-case Max	0.41	°C/W
R_{thc-h}	Thermal Resistance Case-heatsink With Conductive Grease Applied Max	0.05	°C/W

ELECTRICAL CHARACTERISTICS (T_{case} = 25 °C unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
I_{CER}	Collector Cut-off Current (R_{BE} = 5 Ω)	$V_{CE} = V_{CEV}$ $V_{CE} = V_{CEV}$ T_j = 100 °C			0.2 2	mA mA
I_{CEV}	Collector Cut-off Current (V_{BE} = -1.5V)	$V_{CE} = V_{CEV}$ $V_{CE} = V_{CEV}$ T_j = 100 °C			0.2 2	mA mA
I_{EBO}	Emitter Cut-off Current (I_C = 0)	V_{EB} = 5 V			1	mA
$V_{CEO(sus)}$*	Collector-Emitter Sustaining Voltage (I_B = 0)	I_C = 0.2 A L = 25 mH V_{clamp} = 450 V	450			V
h_{FE}*	DC Current Gain	I_C = 60 A V_{CE} = 5 V		15		
$V_{CE(sat)}$*	Collector-Emitter Saturation Voltage	I_C = 30 A I_B = 3 A I_C = 30 A I_B = 3 A T_j = 100 °C I_C = 60 A I_B = 12 A I_C = 60 A I_B = 12 A T_j = 100 °C		0.35 0.5 	 2 2	V V V V
$V_{BE(sat)}$*	Base-Emitter Saturation Voltage	I_C = 60 A I_B = 12 A I_C = 60 A I_B = 12 A T_j = 100 °C		1.1 	 1.5	V V
di_C/dt	Rate of Rise of On-state Collector	V_{CC} = 300 V R_C = 0 t_p = 3 µs I_{B1} = 18 A T_j = 100 °C	150			A/µs
V_{CE}(3 µs)•	Collector-Emitter Dynamic Voltage	V_{CC} = 300 V R_C = 30 Ω I_{B1} = 18 A T_j = 100 °C		4	6	V
V_{CE}(5 µs)•	Collector-Emitter Dynamic Voltage	V_{CC} = 300 V R_C = 30 Ω I_{B1} = 18 A T_j = 100 °C		2	3	V
t_s t_f t_c	Storage Time Fall Time Cross-over Time	I_C = 30 A V_{CC} = 50 V V_{BB} = -5 V R_{BB} = 0.2 Ω V_{clamp} = 400 V I_{B1} = 3 A L = 25 µH T_j = 100 °C		4.5 0.1 0.3	5 0.2 5	µs µs µs
V_{CEW}	Maximum Collector Emitter Voltage Without Snubber	I_{CWoff} = 80 A I_{B1} = 16 A V_{BB} = -5 V V_{CC} = 50 V L = 80 µH R_{BB} = 0.2 Ω T_j = 125 °C	400			V

∗ Pulsed: Pulse duration = 300 µs, duty cycle 1.5 %

Safe Operating Area



Thermal Impedance



Derating Curve



Collector-Emitter Voltage Versus Base-Emitter Resistance



Collector-Emitter Saturation Voltage



Base-Emitter Saturation Voltage



Reverse Biased SOA



Forward Biased SOA



Reverse Biased SOA



Forward Biased SOA



Switching Time Inductive Load



Switching Time Inductive Load Versus Temperature



DC Current Gain



Turn-off Switching Test Circuit



1) Fast electronic switch 2) Non-inductive Resistor

Turn-on Switching Waveforms.



Turn-off Switching Test Circuit



1) Fast electronic switch 2) Non-inductive Resistor
3) Fast recovery rectifier

Turn-off Switching Waveforms.



ISOTOP MECHANICAL DATA

DIM.	mm			inch		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A	11.8		12.2	0.465		0.480
A1	8.9		9.1	0.350		0.358
B	7.8		8.2	0.307		0.322
C	0.75		0.85	0.029		0.033
C2	1.95		2.05	0.076		0.080
D	37.8		38.2	1.488		1.503
D1	31.5		31.7	1.240		1.248
E	25.15		25.5	0.990		1.003
E1	23.85		24.15	0.938		0.950
E2		24.8			0.976	
G	14.9		15.1	0.586		0.594
G1	12.6		12.8	0.496		0.503
G2	3.5		4.3	0.137		1.169
F	4.1		4.3	0.161		0.169
F1	4.6		5	0.181		0.196
P	4		4.3	0.157		0.169
P1	4		4.4	0.157		0.173
S	30.1		30.3	1.185		1.193



P093A

STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.

http://www.st.com